



Rating	3A 125V AC, 1.5A 250V AC 6A 14V DC, 3A 28V DC	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 minute		
Operation Temperature	0°C~85°C		
Switch Function	4P SPST OFF-(ON) (LED Independent)		

***MATERIAL:**

Frame: Black, Nylon 66+30%GF (94-V2)

Actuator: Red clear, PC (94-V2)


LED: Red

Terminals: Silver plated, Copper alloy

Terminal (+,-): Sn plated, Brass alloy

Contacts: Silver plated, Copper alloy

Printed: None



Travel:

To operate is 2.0mm

To full is 3.4mm

Actuation force is 500±200gf

Tolerances ±0.3 Unless Otherwise Specified

08/20/13	柳新強	依實物修正圖面(相圖方向)					△
9/13/10	B.S.Wang	To cancel UL/CUL mark and print LED voltage					△
Date	Name	Description					No.
Drawn	Checked	Approved	SCI BOM No.	1830954	Model Name	PUSH SWITCH	
柳新強	待+112	Simon	Customer No.		Model No.	R13-508AL2-05	Rev.
08/20/13	8/21-13	9/13-13	Unit	mm	Ⓢ Shin Chin Industrial Co., Ltd.		2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R13-508AL2-05](#)