






M4 Screws
SUS304



| | | | |
|---------------------------------|---|----------------|-----------------|
| Voltage (Max.) | 32 VDC. | Mounting Holes | Blade Fuse Dim. |
| Input Terminal Rating | Ø10 mm threaded studs (100A max. tested by 4 pcs. 25A load.) | | |
| Output Terminal Rating | 30A max. per circuit. | Terminal Dim. | |
| Connection Pad Option Available | Input wire size : #4-6 AWG. Output wire size : #12-16 AWG. | | |
| Fuse Specifications | For Blade Fuses Used Only | | |
| Torque Rating | 20 in-lb (2.25Nm) max. | | |
| Mounting Torque Rating | 8 in-lb (0.9Nm) max. | | |
| Temperature Rating | -20 °C to 85 °C | | |

Circuit Diagram



Material :
Cover : PC, Transparent.
Housing , Base : PBT, Red.
Terminal : Tin, plating Copper.

Notes :
Rating 100A max. tested by 4 pcs. 25A load.
Tolerance ±1.0 except noticed

A3

| | | | | | | | |
|----------|----------|-------------|--------------|---------|--------------------------------|----------------|------|
| Drawn | Checked | Approved | SCI BOM No. | 1310880 | Model Name | BLADE FUSE BOX | |
| 洪啟峰 | 許慶發 | 許慶發 | Customer No. | | Model No. | R3-108-07-3104 | Rev. |
| 11/27/19 | 11/29/19 | 11/28/19 | Unit | mm | Shin Chin Industrial Co., Ltd. | | 0 |
| Date | Name | Description | No. | | | | |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R3-108-07-3104](#) [R3-108-07-3L104](#)