










Rating	10A 125V AC, 6A 250V AC 	Mounting Hole	Circuit Diagram
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1000V 1 minute		
Switch Function	2P SPST ON-OFF		



1 HEX NUT ASSY
1 KNURL NUT ASSY
1 SPRING WASHER ASSY



1. Tolerances ±0.3 Unless Otherwise Specified

								△
								△
Date	Name		Description					No.
Drawn	Checked	Approved	SCI BOM No.	1812415	Model Name	TOGGLE SWITCH		
曾敏捷			Customer No.		Model No.	R13-25A2-01		Rev.
06/26/17	6/27-17	6/27-17	Unit	mm	Shin Chin Industrial Co., Ltd.			0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R13-25A2-01](#)