




Rating	10A 125V AC 6.3A 250V AC 1.6W	UL US CSA	<div>Mounting Hole</div> 
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 Minute		
Fuse Size	Ø5*20mm(0.197"*0.788")		

Material:
Frame:Black,Nylon#66(94V-0)
Cover:Black,Nylon#66(94V-0)
Terminal:Silver plated,Copper alloy



Tolerances ± 0.3 Unless Otherwise Specified

									△
									△
Date	Name	Description	No.						
Drawn	Checked	Approved	SCI BOM No.	1310936	Model Name	FUSE HOLDER			
袁浩徐		Simon	Customer No.	112-R3-54B	Model No.	R3-54B		Rev.	
09/24/'19		10/8-19	Unit	mm	Shin Chin Industrial Co., Ltd.			0	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R3-54B](#)