






Rating	Input : 12/24V DC USB socket - 5V 2.1A+2.1A QC3.0 socket - 5V/3A 9V/2A 12V/1.5A±10%
Insulation Resistance	DC 500V 100MΩ Min.
Operating Temperature	-20°C ~ +50°C
Material	Housing: ABS Contact: nickel plated iron Spring Contact: nickel plated spring steel



A13-228WB3

黑飾蓋
白本體

Tolerances ±0.5 Unless Otherwise Specified

			△	Drawn	Checked	Approved	SCI BOM No.	1251767	Model Name	3USB Adapter	
			△	李景山		<i>Since</i>	Customer No.		Model No.	A13-228WB3	REV.
Date	Name	Description	NO	01/15/'19		1/22-19	Unit	mm	Shin Chin Industrial Co., Ltd.		0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[A13-228WB3](#)