












Rating	Operating voltage: 7V~33V DC $\pm 2\%$ (0.24V @ 12V, 0.48V @ 24V) Measuring Voltage: 7~33V Long time use suggestion to 0~70A Measuring Current range: 0~100.0A $\pm 3\%$ 10A $\pm 0.3A$, 50A $\pm 1.5A$, 100A $\pm 3.0A$ LED digital display. Reverse polarity protection. Surge protection up to 400W/36V
Insulation Resistance	DC 500V 100M Ω Min.
Operating Temperature	-20°C~50°C



原稿
2018.7.19
研發部

Tolerances ± 0.5 Unless Otherwise Specified

				Drawn	Checked	Approved	SCI BOM No.	1570034	Model Name	DC Volt / Amp meter		
				Rock Hsu			Customer No.	112-A25-7-BB3-R	Model No.	A25-7-BB3-R	Rev.	0
Date	Name	Description	No.	06/26/18		06/26/18	Unit	mm	Shin Chin Industrial Co., Ltd.			

for SCI

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[A25-7-BB3-R](#)