

NOTES:

TAPE AND REEL SPECIFICATIONS:

1. TAPE:

MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER  
ANSI/EIA-481 STANDARD  
.945 [24.0] WIDE; .630 [16.0] PITCH





2. REEL:

15.0 [381.0] DIA. 800 PIECES OF  
PART NO. 983 PER REEL.

10.17.06	CHANGE AS PER ECN 06-066	A
DATE	DESCRIPTION	REV.

KEYSTONE ELECTRONICS CORP.			
www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900			
PART NAME			
3.5mm SM MONO JACK ON TAPE			
MATERIAL			
AS NOTED			
FINISH		DRN BY	DATE
AS NOTED		BOONE	2.28.00
		APP'D	SCALE
		LN	X
TOLERANCES	INCH [MM]	CODE	DWG NO.
DECIMAL	± .015 [± 0.38]	C	983TR
ANGULAR	± 1°		
UNLESS OTHERWISE SPECIFIED			

# ACTUAL SIZE



## NOTES:

- MAT'L:**  
HOUSING: LCP, UL 94V-0  
GROUND TERMINAL: .012 [0.3] TH'K BRASS ①  
SPRING CONTACT: .008 [0.2] TH'K PHOSPHOR BRONZE ⑤  
SHUNT TERMINAL: .012 [0.3] TH'K BRASS ④
- TAPE SPECIFICATIONS:**  
MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER  
ANSI/EIA-481 STANDARD  
24MM (.945) WIDE; 16MM (.630) PITCH
- REEL SPECIFICATION:**  
15 INCH DIA. 800 PIECES

5.20.13 HOUSING WAS POLYAMIDE  
CHANGE AS PER ECN 13-041

A

REV.

## KEYSTONE ELECTRONICS CORP.

www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900

PART NAME

3.5mm SURFACE MOUNT MONO JACK

MATERIAL

AS NOTED

FINISH

GOLD FLASH

DRN BY

BOONE

DATE

5.14.99

APP'D

LN

SCALE

3X

TOLERANCES

INCH

[MM]

DECIMAL

± .005 [± 0.13]

ANGULAR

± 1°

UNLESS OTHERWISE SPECIFIED

CODE

DWG NO.

983

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Keystone Electronics:](#)

[983TR](#)