


Balanced Armature Driver

SR-32453-000


Single Full-range

Product Features:

- Lowest cost
- Optimized performance for entry-level
- Round form factor
- RoHS compliant



Outline Drawing mm (inches)



Demonstrator Earphone Model Number

(standard sample in BOLD)

	without MIC	with MIC
Straight Cable	TC-32211-B107	TC-32282-B107

Ordering Information:
Model Number: SR-32453-000

Phone: (630) 250-5100
Fax: (630) 250-0575
info@knowles.com


Knowles
1151 Maplewood Drive
Itasca, Illinois 60143

Balanced Armature Driver


SR-32453-000

Single Full-range

Frequency Response and THD



Impedance and Saturation SPL



Testing Conditions

- using 100mV rms drive signal
- IEC60318-4 (711) coupler with DB2012 adapter
- G.R.A.S. 43BA-2 (0.4cc) with baffle adapter
- THD
- All test conditions use small eartip size

Typical Performance at 1kHz

Impedance	50	Ohms
Sensitivity to 100mV	104	dB SPL
Sensitivity to 1mW	111	dB SPL
Max SPL ^a	118	dB SPL
THD at 94dB SPL	0.3	%
THD at 100dB SPL	0.4	%

Footnotes:

^a SPL at 10% THD

- Note:
- Ask about custom assembly options (lead wires, customer-specified materials, etc.)
 - To prevent heat damage, follow soldering guidelines in application note AN13 (knowles.com)
 - Measurement data for reference only. Refer to model specification for full dimensions and performance.

Ordering Information:
Model Number: SR-32453-000

Phone: (630) 250-5100
Fax: (630) 250-0575
info@knowles.com

Knowles
1151 Maplewood Drive
Itasca, Illinois 60143

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Knowles:

[SR-32453-000](#)