





features

- Metal glaze resistors (RuO_2) provide lifetime stability
- Free from short circuit, unexpected solder melting and terminal disconnection due to the high temperature solder used to connect terminals
- Capable of reducing the numbers of parts and part insertions
- Custom orders are available
- Products with lead-free termination meet EU RoHS requirements. EU RoHS regulation is not intended for Pb-glass contained in electrode, resistor element and glass

dimensions and construction



Type	Dimensions inches (mm)			
	Number of Pins	L	H	p
CRA	5 - 9	.100xP+.024 (2.54xP+0.6)	.256 (6.5)	.100 (2.54)
CRB	5 - 10			
CRC	5 - 13			
CRD	5 - 13			
CRE	6 - 14			
CRF	5 - 13			

□ = Number of pins

ordering information

CR	E	6	01	D
Product Code	Circuit Symbol	Number of Cells	KOA Reference Number	Terminal Surface Material
	A B C D E F M	4 - 8 (CRA) 3 - 8 (CRB) 2 - 6 (CRC, CRD CRE, CRF) Nil (CRM)		D: SnAgCu Nil: Sn/Pb

ratings

Parameter	Resistor	Capacitor
Max. Operating Voltage	50V	
Constant Range	10Ω - 1MΩ	10pF - 0.1μF
T.C.	±200x10 ⁻⁶ /K	CH, B, R*
Tolerance	±5% (J)	±5% (J) ±10% (K) ±20% (M)
Operating Temp. Range	-25°C - +85°C	
Storage Temp. Range	-55°C - +125°C	


T.C. Type	T.C.			
	Reference Temp.	Temp. Range	Capacitance Change or Temp. Coefficient	Operating Temp.
CH	20°C	20°C~125°C	0±60X10 ⁻⁶ /K	-55°C~125°C
B	20°C	-25°C~85°C	±10%	-25°C~85°C
R	20°C	-55°C~125°C	±15%	-55°C~125°C

maximum wattage/package

	Number of Pins				
	5	6	7	8	9
mW/Package	500	625	750	875	1000

	Number of Pins				
	10	11	12	13	14
mW/Package	1050	1150	1250	1350	1450

circuit schematics



When ordering the CR series, please indicate the following items shown below:

For circuit code A – F, please indicate the following items:

Resistance
Capacitance
Operating voltage
Capacitance tolerance
T.C.

For circuit code M, please add the following items:

Circuit schematics
Pin layout
Dimensions
Conditions for use
Resistor (Power rating, Tolerance, T.C.R.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KOA Speer:](#)

[CR2A10YTTE101M/820J](#) [CR2A10YTTE470M/470J](#) [CRBS03LTE470J/470M](#)