



Copyright 2006


ANDERSON POWER PRODUCTS RESERVES THE RIGHT TO ALTER PRODUCT TYPES, THEIR TECHNICAL DATA, DIMENSION, STYLE AND ACCESSORIES WITHOUT PRIOR NOTIFICATION.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ANDERSON POWER PRODUCTS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF ANDERSON POWER PRODUCTS IS PROHIBITED.

ACTUAL SIZE



NO ORIENTATION



SECTION VIEW
SHOWN LOADED INTO HOUSING

P/N	A		B		C		D		E	
	IN	mm	IN	mm	IN	mm	IN	mm	IN	mm
SS20-GN	.05	1.3	.08	2.1	.08	2.1	.20	5.0	1.00	25.5
SS16-SN	.08	2.0	.11	2.9	.11	2.9	.22	5.5	1.00	25.4
SS12-SN	.11	2.8	.15	3.8	.16	4.1	.24	6.0	1.00	25.5
SS08-SN	.19	4.8	.24	6.0	.21	5.3	.39	10.0	1.24	31.5
SS12-GH	.11	2.8	.15	3.8	.16	4.1	.24	6.0	1.00	25.4

NOTES:

- SS08-SN FOR USE IN 75 AMP POWER DRAWER ONLY
- SOLDER CONTACTS ONTO WIRE PRIOR TO INSERTION INTO HOUSING
- MATERIALS: SOCKET BODY- BRASS
SOCKET INSERT- BeCu
- PLATING: SOCKET INSERTS- GOLD OVER NICKEL
"-SN" PART NUMBERS: BODY IS PLATED SILVER OVER NICKEL
"-GN" PART NUMBERS: BODY IS PLATED GOLD OVER NICKEL
"-GH" PART NUMBER: BODY IS PLATED GOLD OVER NICKEL AND HOT PLUGGABLE

DIMENSIONS ARE IN: INCH[MM]		DRAWN	CMS	3/2/06	 ANDERSON POWER PRODUCTS	
UNLESS OTHERWISE STATED		CHECKED	DJD	3/8/06		
TOLERANCES:		MFG APP	CHB	3/2/06	TITLE SOCKET SOLDER CONTACTS FOR POWER DRAWER SERIES CONNECTORS	
DECIMALS (INCH)	DECIMALS (MM)	ANGLES	QC APP	JA		
.XX ± .02	.X ± .5	± 2°	ENG APP	DAM		
SURFACE FINISH:			PROD MGR	MK	3/2/06	SIZE A/A4
MACHINED 128 [3.2]✓			-CAD GENERATED DRAWING- DO NOT MANUALLY UPDATE DO NOT SCALE		DWG NO.	REV.
MOLDED 64 [1.6]✓					114564S1	1
MATERIAL: SEE NOTES		FINISH: SEE NOTES		SCALE	CADFILE	SHEET
				NONE	02179	1 OF 1

1	ECRN 14415: SHOW THRU HOLE, ADD SS12-GH	CHB	4/11/09
REV.	DESCRIPTION OF CHANGES	APPROVED	DATE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anderson Power Products:](#)

[SS12-GH](#)