

ORDERING INFORMATION

Tooling


Part Number	Description
1387G3	Hydraulic tool for power contacts
E160-36	Extraction tool

Note: For tooling die information, see tooling chart on website.

DIMENSIONS


Pin Contact

Part Number	- Wire -		- ØA -		- ØB -		- C -	
	mm ²	AWG	mm	in.	mm	in.	mm	in.
320-1050	50	#1/0	14.5	0.57	11.0	0.43	65.5	2.58
320-1070	70	#2/0	17.0	0.67	13.0	0.51	65.5	2.58
320-1095	95	#3/0	19.8	0.78	15.0	0.59	70.5	2.78




Upper Auxiliary Contact

E320-34 upper auxiliary contact for 4 mm² (#12 AWG)




Lower Auxiliary Contact


160-12 lower auxiliary contact for 6 mm² (#10 AWG)





Handle / Lever Assembly / Latch




Housing Front View




TEMPERATURE CHARTS



Housing Side View



Housing Top View



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Anderson Power Products:

[320-1003](#) [320-1035](#) [320-1050](#) [320-1070](#) [E320-20](#) [E320-21](#) [E320-89](#) [E32404-1049](#) [E32404-10C9](#) [106G17](#)
[106G18](#) [E32500-0009](#) [E32570-0269](#) [E32500-0008](#) [E32570-1048](#) [E32570-0229](#) [E32450-1349](#) [E32570-0008](#)
[E32450-1309](#) [E32570-1069](#) [E32570-0349](#) [E32570-0329](#) [E32470-1229](#) [E32435-0009](#) [E32470-0048](#) [E32470-1269](#)