


XPort® EDGE

xPico® 270

xPico® 250

xPico® 240

PremierWave® 2050

xPico Wi-Fi®

Features	XPort® EDGE	xPico® 270	xPico® 250	xPico® 240	PremierWave® 2050	xPico Wi-Fi®
Category	Wired Device Server	Now Available		Wireless IoT Gateway		Wireless Module
Mounting Option	Connector	Connector/SMT	Connector/SMT	Connector/SMT	Connector/SMT‡	Connector/SMT‡
Operating System	ThreadX	ThreadX	ThreadX	ThreadX	Linux	ThreadX
10/100 Ethernet	•	External RJ45 Jack/Magnetic Module/PHY	External RJ45 Jack/Magnetic Module/PHY	External RJ45 Jack/Magnetic Module/PHY	External RJ45 Jack/Magnetic Module	
Wireless 802.11		a/b/g/n/ac	a/b/g/n	a/b/g/n	a/b/g/n/ac	b/g/n
Bluetooth®/ Bluetooth Low Energy		5.0	5.0		4.2	
Antenna Options		External	External	On Module or External‡	On Module or External‡	On Module or External‡
LAN > 802.11 Bridging		•	•	•	•	
Simultaneous Soft AP and Client		•	•	•	•	•
Enterprise Wi-Fi Security		•	•	•	•	
SmartRoam™		•	•	•		
TCP / UDP Client-Server	•	•	•	•		•(tUDP)
Telnet					•	
DHCP, BOOTP & AUTOIP	•	•	•	•	•	•
FIPS 140-2 Level 1	•†	•†	•†	•†	•	
SFTP					•	
SNMP	v1/v2	v1/v2	v1/v2	v1/v2	v1/v2/v3	
Modbus (*Available in IAP)						
Web Server - HTTP/CGI (*Custom)	•	•*	•*	•*	•	•
Web Server - AJAX	•	•	•	•*	•	•
SSL Secure Web Server	•	•	•	•	•	
SSL Secure Data Tunneling	•	•	•	•	•	
SSH Client & Server					•	
IPv6 (*Linux SDK Development Platform)	•	•†	•†	•†	•	•†
AES Encryption	•	•	•	•	•	•
Max Configurable GPIO Pins (*RTS/CTS on Configurable Pins)	3*	12	12	12	13	8
Software Development Kit	•	•	•	•	•* (Yocto)	
Flash/RAM	8MB/2MB	8MB/2MB	8MB/2MB	8MB/2MB	256MB/128MB	1MB/128KB
Maximum Serial Data Rate	4 Mbps	4 Mbps	4 Mbps	4 Mbps	921 Kbps	921 Kbps
Web Manager (for Configuration)	•	•	•	•	•	•
Email Client (*Subject Line Only)	•	•	•	•	•	
Operating Temperature (C°/F°)	-40 to 85°C / -40 to 185°F	-40 to 85°C / -40 to 185°F	-40 to 85°C / -40 to 185°F	-40 to 85°C / -40 to 185°F	-40 to 85°C / -40 to 185°F	-40 to 85°C / -40 to 185°F
Dimensions (mm; +/-0.3mm)	33.9 x 16.25 x 13.5	17 x 25 x 2 (LGA) 22 x 33.5 x 2.73 (Edge Card)	17 x 25 x 2 (LGA) 22 x 33.5 x 2.73 (Edge Card)	17 x 25 x 2 (LGA) 22 x 33.5 x 2.73 (Edge Card)	46.66 x 45.07 x 3.5	SMT (1002): 301 x 18.3 x 3.0 SMT (1003): 261 x 18.3 x 3.0 24 x 16.5 x 5.64
SPI Interface		•	•	•	•	•†
USB (*Full Speed Only)		Device & Host	Device & Host	Device & Host	Device & Host	•*

† Available in future software release ‡ Version dependent

Lantronix Corporate Headquarters

7535 Irvine Center Dr., S. 100, Irvine CA 92618
t: 800.422.7055
sales@lantronix.com

EMEA Sales

t:+31 (0)76 52 36 744
eu_sales@lantronix.com

Asia/Pacific Sales

t: + 852 3955 0218
asiapacific_sales@lantronix.com

India Sales

t:+91 994 551 2488
sales_india@lantronix.com

© 2020 Lantronix, Inc. All rights reserved. Lantronix, xPico, XPort and PremierWave are registered trademarks of Lantronix Inc. in the U.S. and certain other countries. Evolution OS, Connect Smart, Do More., and SmartRoam are registered trademarks or trademarks of Lantronix Inc. Wi-Fi® is a registered trademark of Wi-Fi Alliance®. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Lantronix is under license. All other trademarks are the property of their respective owners. Specifications subject to change without notice. MPM-00001 Rev E

LANTRONIX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lantronix:](#)

[XPE200100EK](#)