



# SpiderDuo KVM

Secure KVM-over-IP  
with Local Access



## COMPACT KVM-OVER-IP PLUS LOCAL ACCESS FOR DISTRIBUTED SERVER MANAGEMENT

The Lantronix® SpiderDuo KVM is the newest in the popular Spider family of remote KVM solutions. SpiderDuo provides secure, remote KVM (keyboard, video and mouse)-over-IP capabilities, as well as transparent local access.



### Flexible KVM-over-IP

The SpiderDuo is ideal for those who need local access, as well as the flexibility of KVM-over-IP in a single integrated solution. Its palm-sized, “zero-U” design is perfect for space-constrained applications. What’s more, SpiderDuo requires no additional software and allows full BIOS level control of the host system.



### Secure Remote Management

SpiderDuo makes administration a breeze. Using integrated Virtual Media, users can transfer files, perform upgrades, install patches, redirect local drives and perform full system upgrades by ISO file. Coupled with the optional single port PCU (power control unit), authorized users can also initiate power cycling over the network.

SpiderDuo allows complete local, plus remote management of the host machine anytime, from virtually anywhere. It provides reliable, secure access to servers located in data centers, kiosks, regional offices, campuses, ATMs, point of sale (POS), training centers, or test and development labs.



### Perception™ Cloud Management

Enterprise-class device management is available with the Perception Cloud Management Platform. Perception provides remote updates at scale using device groups to deliver software enhancements and security patches worldwide, reducing time, effort and cost. Configurations can be performed on a single device, or a template can be created to update groups of devices.

### SpiderDuo Highlights

- Reduce costs and decrease downtime by remotely managing PCs and servers, down to the BIOS level, while still allowing transparent local access
- Transfer files, install patches, perform upgrades remotely with Virtual Media
- Remotely manage power with the optional power control unit
- Easy configuration and installation with color coded connectors—local and remote management are up and running in minutes

### Target Applications:

- Data centers and development labs
- Retail kiosks
- Banking ATMs
- Point-of-sale (POS)

### Target Markets:



Enterprise



Retail



Financial  
Services

## Features and Specifications

### Security

- Hardware based encryption of keyboard, mouse and video data
- IP Source Address Filtering
- Remote Authentication: LDAP, RADIUS, Active Directory
- User/Group management with permissions control
- Configurable port numbers (HTTP, HTTPS, Telnet, SSH)
- Selective disable of Telnet/SSH

### Access

- Local access and up to 8 simultaneous remote users

### Target Server Requirements

- Supports Multiple Operating Systems: Windows® 11/10/ Vista/7, Unix, Linux, or MAC OS X®
- Keyboard/mouse: 1 USB and 1 mouse
- Video Interface: HD15 VGA video output (up to 1600x1200@60Hz)

### Client System Requirements

- Internet Explorer® 6.0+, Netscape 5.0+, Firefox® 3.0+, Safari® 2.0+
- PIII Processor equivalent or better (recommended)
- Google Chrome 107+
- Telnet/SSH client for command line (CLI) access

### Interfaces

- Network: 10/100/1000Base-T Ethernet Port with activity indicators (RJ45)
- Serial: RS-232, up to 115,200 bps for serial device pass-through, unit configuration or PCU controller
- USB and/or PS/2
- Local KVM connector
- Computer input connector

### Cables

- Includes local KVM and computer input USB or USB and PS/2, 21.6"

### Environmental

- Operating: 0° to 45° C (32° to 115° F) condensing)
- Storage: -20° to 70° C (-4° to 158° F)
- Humidity: 0 to 95% RH (non- condensing)
- Heat Dissipation: 4-8 Watts (14-28 BTU/hr)

### Power Requirements

- Input: 5 VDC @ 2A max.

### Certifications

- FCC
- IC
- CE
- UKCA
- UL/CB
- RoHS

### Warranty

- 2-year limited warranty

### Form Factor

- Dimensions: (H x W x D) 13.2 x 5.8 x 3.6 cm (5.2 x 2.3 x 1.4 in)
- Weight: USB: 269g (9.50 oz)

## Ordering Information

Part Number	Description
SLSLP400USB-02	1 Port Local plus Remote KVM-over-IP with USB Connectors; 21.6" VGA cables
SLSLP400PS2-02	1 Port Local plus Remote KVM-over-IP with PS/2 Connectors; 21.6" VGA cables

## Accessories

Part Number	Description
PCU100-01	Single port power control unit, 100-240VAC, 50/60Hz, 10A (Includes IEC320/C13 to NEMA inlet and IEC320/C14 to IEC320/C13 outlet power cables)
ACC-500-199-R	Extended length cable (computer input) USB connector; 59" VGA cable
500-200-R	Extended length cable (computer input) PS/2 and USB connectors; 59" VGA cable
ACC-520-0203-00	Replacement DC Power Supply with International Adapters (100-240VAC, 50-60 Hz; 5 VDC @ 2A)

## Contact Information

### Americas

americas\_sales@lantronix.com  
www.lantronix.com  
NASDAQ: LTRX

### Europe

eu\_sales@lantronix.com

### Asia/Pacific

asiapacific\_sales@lantronix.com



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lantronix:](#)

[SLSLP400USB-02](#) [SLSLP400PS2-02](#)