




# LTE Cellular Connectivity Kit

IT Management



## 4G LTE BASED CELLULAR OUT-OF-BAND MANAGEMENT SOLUTION FOR LANTRONIX SLC™ 8000 ADVANCED CONSOLE MANAGER AND SLB™ BRANCH OFFICE MANAGER

The LTE Cellular Connectivity Kit is an industrial-grade 4G LTE wireless solution offering cellular back-up with automatic fail-over for your Lantronix IT Management products.

### Flexible & Robust

The LTE Connectivity Kit provides reliable 4G LTE connectivity via an industrial-grade and secure gateway designed to provide an enterprise-level remote connectivity solution. With state-of-the-art global LTE coverage, the LTE gateway provides broadband connectivity for Lantronix IT Management solutions.

### Automatic Fail-over

The Lantronix LTE Cellular Connectivity Kit delivers mission-critical LTE connectivity as a failover solution to protect your data center and branch office out-of-band management infrastructure against landline failure. With new automatic fail-over functionality built into your Lantronix SLC 8000 Advanced Console Manager and SLB Branch Office Manager, deployment of a secondary enterprise network connection is simple and quick, and automatic fail-over from a land-line network outage is seamless.

### Simple & Elegant Set-up

The Lantronix LTE Connectivity Kit has been fully integrated and validated with the Lantronix SLC 8000 Advanced Console Manager and the Lantronix SLB Branch Office Manager for quick set up and seamless provisioning. Through the Lantronix user interface, the user experience is optimized for a simple and straightforward set-up routine.

### Product Highlights

- Full-featured LTE gateway for failover and failback connectivity
- State of the art LTE coverage spanning 11 LTE frequency bands
- Supports present and future high-speed LTE networks
- Cellular out-of-band management for remotely troubleshooting and restoring enterprise IT equipment using Lantronix IT Management products
- Reliable Static Route eliminates redundant wireless data usage
- Set-up and provisioning via Lantronix SLC 8000 Advanced Console Manager and SLB Branch Office Manager
- Enterprise-grade design for data center and remote office use



LANTRONIX



## Features and Specifications

### North American Model

- Carrier Approvals: Verizon®, AT&T®, Sprint®, T-Mobile® USA, US Cellular®, Rogers®, Bell®, Telus®

### Supported Frequency Bands

- LTE: 1900(B2), AWS(B4), 850(B5), 700(B13), 700(B17), 1900(B25)
- WCDMA: 2100(B1), 1900(B2), AWS(B4), 850(B5), 900(B8)
- EV-DO/CDMA: 800(BC0), 1900(BC1), 1700(BC10)
- GSM/GPRS/EDGE: Quad-band
- Industry Approvals: FCC, IC, PTCRB
- SIM Interface (2FF)

### International Model

### Supported Frequency Bands

- LTE: 2100(B1), 1800(B3), 2600(B7), 900(B8), 800(B20)
- WCDMA: 2100(B1), 1900(B2), 850(B5), 900(B8)
- GSM/GPRS/EDGE: Quad-band
- Industry Approvals: CE, RCM, GCF, R&TTE
- Automatic SIM based network operator switching
- SIM Interface (2FF)

### Host Interface

- 10/100 Base-T RJ45 Ethernet port
- 2 SMA antenna connectors (Primary, Secondary/Diversity)

### LAN (Ethernet)

- DNS, DNS Proxy
- DHCP Server
- IP Passthrough
- VLAN
- Host Interface Watchdog
- PPPoE

### Network and Routing

- Network Address Translation (NAT)
- Port Forwarding
- Host Port Routing
- NEMO/DMNR
- VRRP
- Reliable Static Route
- Dynamic DNS

### VPN

- IPsec, GRE, and SSL VPN Client
- Up to 5 concurrent tunnels
- Split Tunnel
- Dead Peer Detection (DPD)
- Multiple Subnets
- VPN Failover

### Dimensions

- 142 x 98 x 41 mm (5.6 x 3.9 x 1.6 in), 397g (14oz.)

### Power

- Input Voltage: 9 to 36 VDC

### Management Interfaces

- Web-Based User Interface via Lantronix ITM UI
- Software and radio module firmware updates directly via Lantronix SLC 8000 Advanced Console Manager and SLB Branch Office Manager

### Environmental

- Operating Temperature: -20°C to +60°C / -4°F to +140°F
- Storage Temperature: -30°C to +70°C / -22°F to +158°F
- Military Spec MIL-STD-810G conformance to shock, vibration

### Industry Certifications

- IECEE Certification Bodies Scheme (CB Scheme)
- UL 60950
- Environmental: RoHS, REACH, WEEE

### Support and Warranty

- 3-year standard warranty

### Set-up and Provisioning via



SLC® 8000  
Advanced Console Manager



SLB™  
Branch Office Manager

## Ordering Information

| Part Number  | Description                                   |
|--------------|---|
| CCKLTE450-NA | LTE Cellular Connectivity Kit - North America |
| CCKLTE450-EA | LTE Cellular Connectivity Kit - Europe/Asia   |

## Contact Information

### Americas

800.422.7055  
sales@lantronix.com  
http://www.lantronix.com  
NASDAQ: LTRX

### Europe

+31 (0) 76.52.3.6.74 4  
EMEA@lantronix.com

### Asia/Pacific/Japan

+852 3428.2338  
asiapacific\_sales@lantronix.com

China: +86.21.6237.8868  
shanghai@lantronix.com

India: +91 994.551.2488  
sales\_india@lantronix.com

Indonesia: +91 994.551.2488  
sales\_indonesia@lantronix.com

Japan: +81 (0) 50.1354.6201  
sales\_japan@lantronix.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lantronix:

[CCKLTE450-EA](#) [CCKLTE450-NA](#)