

CTH10 Radio Controlled Wall Clock + Hygro-Thermometer



This attractive wall clock features an oversized 4.3" (109mm) digit time display that can be easily view from a longer distance than regular sized clocks. It receives Time Code from NIST Radio Station WWVB and it automatically adjusts year, date, day, hour, minute, second, and Daylight Savings Time. In addition, it also measures Temperature and Relative Humidity! Perfect for desktop or wall mount display.



Features

- Receives Time Code from NIST Radio Station WWVB (North American region) to maintain accuracy within 1 second (North America region)
- Signal indicator displays signal strength in 3 levels to indicate successful synchronization
- LCD displays Time, Relative Humidity, Temperature, Year, Month, Date, and Day
- Time can be displayed as 12 or 24 hour format
- Large 4.3" (109mm) digit clock display can be easily viewed from a distance
- Automatically adjusts for daylight savings time (DST)
- Programmable Alarm Clock with Snooze feature
- Built-in stand for desktop or wall-mount
- Complete with built-in stand and three C size batteries

Specifications	Range	Basic Accuracy
Relative Humidity	20 to 99%RH	±6%RH
Temperature	32 to 122°F (0 to 50°C)	±2°F/1°C
Alarm Clock	Yes	
Alarm Snooze	Yes	
Dimensions	16.75 x 11.5 x 1.25" (425.4 x 292.1 x 31.75mm)	
Weight	2.75lbs (1.2kg)	

Ordering

CTH10A Radio Controlled Wall Clock + Hygro-Thermometer

UPC Code: 793950445112

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[CTH10A](#)