

Digital Voltage Tester with Bargraph

 **Voltage, Continuity and Phase Tester with Flashlight and backlit digital display with bargraph; Double molded IP64 housing**
with Built-in flashlight for testing in tight areas

Features:

- Large backlit LCD display
- LCD AC/DC voltage indication:
6V, 12V, 24V, 50V, 230V, 400V, 690V
- Polarity detection with LEDs for positive and negative DC
- Continuity Test with audible tone
- Two handed operation for low impedance testing
- Built-in flashlight for testing in tight areas
- Rubberized double-molded IP64 housing
- EN61010-1 CAT IV 600V and CAT III 600V safety rating
- Dimensions: 9.4x3x1.6" (240x78x40mm)
Weight: 8.4oz (237g)
- Complete with 2 AAA batteries, protective cap, and pouch case



Protective cap included

Ordering Information:

VT30LCD Multifunction Voltage Tester



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[VT30](#)