




SVLT Series 3.6V

3.6V

■ Features


- Higher temperature
- Quick charge & discharge
- RoHS compliant
- clocking circuit
- Automatic meter reader
- Controller
- Toys



Items	Characteristics		
Rated Voltage	3.6V		
Operating Temperature Range	-25 ~+85°C		
Surge Voltage	4V		
Capacitance Range	0.22~1.5 F		
Capacitance Tolerance (25°C)	-20~+80%		
Temperature Characteristics	The specifications shall be met at category temperature range from -25°C to 85°C	Capacitance range	Within 30% of the value at 25°C
		ESR	Less than 2 times of the initial specified value
High Temperature Loaded	The specifications shall be met after rated voltage applied at 85°C for 1000 hours	Capacitance range	Within 30% of the initial value
		ESR	Less than 4 times of the initial specified value
High Temperature Storage	The specifications shall be met after storage at 85°C for 1000 hours	Capacitance range	Within 30% of the initial value
		ESR	Less than 4 times of the initial specified value

Dimensions

mm





SVLT Series 3.6V

Standard Ratings for SVLT Series

Part No.	V	F	TYPE	ESR (Ω ,@1kHz)	Leakage Current mA	ØD	H	P
SCMDVLT3R6224ZVC135007E	3.6	0.22	C	75	0.003	13.5	7.0	5.0
SCMDVLT3R6224ZVH115004E	3.6	0.22	H	75	0.003	11.5	4.5	10
SCMDVLT3R6224ZVV115004E	3.6	0.22	V	75	0.003	11.5	4.5	5.0
SCMDVLT3R6334ZVC135007E	3.6	0.33	C	50	0.005	13.5	7.0	5.0
SCMDVLT3R6334ZVH115004E	3.6	0.33	H	50	0.005	11.5	4.5	10
SCMDVLT3R6334ZVV115004E	3.6	0.33	V	50	0.005	11.5	4.5	5.0
SCMDVLT3R6474ZVC135007E	3.6	0.47	C	50	0.005	13.5	7.0	5.0
SCMDVLT3R6474ZVH115004E	3.6	0.47	H	50	0.005	11.5	4.5	10
SCMDVLT3R6474ZVV115004E	3.6	0.47	V	50	0.005	11.5	4.5	5.0
SCMDVLT3R6105ZVC205007E	3.6	1	C	30	0.008	20.5	7.5	5.0
SCMDVLT3R6105ZVH190004E	3.6	1	H	30	0.008	19.0	4.5	20
SCMDVLT3R6105ZVV190004E	3.6	1	V	30	0.008	19.0	4.5	5.0
SCMDVLT3R6155ZVC205007E	3.6	1.5	C	30	0.008	20.5	7.5	5.0
SCMDVLT3R6155ZVH190004E	3.6	1.5	H	30	0.008	19.0	4.5	20
SCMDVLT3R6155ZVV190004E	3.6	1.5	V	30	0.008	19.0	4.5	5.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lelon:

<u>SCMDVLT3R6105ZVH190004E</u>	<u>SCMDVLT3R6155ZVH190004E</u>	<u>SCMDVLT3R6224ZVC135007E</u>
<u>SCMDVLT3R6224ZVV115004E</u>	<u>SCMDVLT3R6334ZVC 135007E</u>	<u>SCMDVLT3R6224ZVH115004E</u>
<u>SCMDVLT3R6474ZVV115004E</u>	<u>SCMDVLT3R6105ZVC205007E</u>	<u>SCMDVLT3R6334ZVV115004E</u>
<u>SCMDVLT3R6105ZVV190004E</u>	<u>SCMDVLT3R6155ZVV190004E</u>	<u>SCMDVLT3R6474ZVC 135007E</u>
<u>SCMDVLT3R6474ZVH115004E</u>	<u>SCMDVLT3R6334ZVH115004E</u>	<u>SCMDVLT3R6155ZVC205007E</u>