RIGHT ANGLE ANGLISSIMO PLUGS



One plug, eight cable outlets

The Anglissimo plug is an eight in-one plug that can be adapted by the user to all space constraints. You can choose by yourself the best cable outlet need for your application even after the soldering process.

This new elbow connector design allows to adjust and position the connector in an efficient way in order to prevent cable snaging. Each connector can be orientated during its assembly and enables 8 positions. The connector then remains securely positioned in its orientation.

Features:


- 8 in 1 plug
- Cable clarity
- Clean design
- Reduce operating failures caused by stressed cables






Model

FS• Adjustable right angle plug



Reference		Dimensions (mm)						Spanner
Model	Series	А	Н	L	М	S1	S2	part number
FSe	00	8.0	18.1	24.8	16.8	5	7	DCP.91.FSG.TN
FSe	0B	10.0	22.4	30.3	20.3	7	9	DCP.91.FSG.TN
FSe	1B	12.0	26.4	36.5	25.5	9	11	DCP.91.FSG.TN
FSe	2B	16.5	34.5	44.0	32.0	12	15	DCP.91.FSG.TN

Note: ● = alignment key. See unipole-multipole catalogue.



For insert types and collet sizes see unipole-multipole catalogue.

LEMO HEADQUARTERS

SWITZERLAND

Chemin des Champs-Courbes 28 - P.O. Box 194 - CH-1024 Ecublens Tel. (+41 21) 695 16 00 - Fax (+41 21) 695 16 02 - e-mail: info@lemo.cor

www.lemo.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

 FPG.1B.307.CYCD52
 FGL.1B.308.CLLD76
 FPG.1B.306.CLAD62
 FSG.1B.316.CLAD72Z
 PHI.1B.308.CYMD62Z

 EYG.1B.304.CLN
 PHG.1B.303.CYZZ
 FGE.1B.310.CLAD76
 FGG.1B.155.LNNT