

SUMMARY

Wires

Low voltage 6



Image is for illustrative purpose only

Series	2P
Termination type	Male crimp
IP rating	50
AWG wire size	28.00 - 20.00
Cable Ø	7.30 - 9.20 mm
Status	active
Matching parts	CKB.M06.GYMN

Download

[Request a quote](#)

[Eplan](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	CA*: Straight plug with cable collet and nut for fitting a bend relief
Keying	3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts)
Housing Material	PSU (Polysulfone), gray
Weight	9.81 g

Performance

Configuration	2P.M06 : 6 Low V.
Insulator	Y: PEEK for crimp contacts
Rated Current	12 Amps

Specifications

Test voltage (kV rms) Contact-contact: 1.35
Air clearance min.: 1.52 mm
Creepage distance min.: 1.52 mm


Others

Endurance (Shell): >1000 mating cycles
Temp (min / max): -50°C / +150°C
F ret (min): 150 N

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

F ret (max): 250 N
Steam sterilization: 20 times (with potting on rear connection)

DRAWINGS



RECOMMENDED BY LEMO

Tools

- Crimp Tool: [DPC.91.701.V](#)
- Crimp settings: AWG/Selector = 18-20/8-7
- Positionner: [DCE.91.132.BVC](#)
- Extractor: [DCF.91.131.2LT](#)
- Replacement contact: FGG.2B.565.ZZC

Cables

360500	PVC	Grey	
360750	PVC	Grey	

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[CAB.M06.GYC.C92NZ](#)