

## SUMMARY

### # Wires

High voltage 8



*Image is for illustrative purpose only*

Series 2P  
Termination type Male solder  
IP rating 50  
AWG wire size 0.00 - 0.00  
Cable Ø 3.20 - 5.20 mm  
Status active

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model CA\*: Straight plug with cable collet  
Keying  
Housing Material PSU (Polysulfone), black  
Weight 8.23 g

### Performance

Configuration 2P.H08 : 8 High Voltage  
Insulator  
Rated Current 6.5 Amps

### Specifications

Test voltage contact-contact : 10.3 kV rms  
Air clearance min.: 7.42 mm  
Creepage distance min.: 7.42 mm


### Others

Temp (min / max): -50°C / +150°C

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

---

## DRAWINGS



---

## RECOMMENDED BY LEMO

### Tools

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[CAD.H08.NLA.C52R](#)