

DETAILS

Wires

Low	4
High	0
Coax	0
Triax	0
Quadrax	0
Fiber	0
Fluidic	0

Colour	GREY
UL	yes
ROHS	yes
Material	PVC
AWG	22

Description	LEMO Standard cable - DIN 47100 AWM2464
-------------	--



Image is for illustrative purpose only

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Dimensions

Core diameter	.74 mm
Sheath diameter	4.70 mm
Shielded	with shielding
Ohms	-
Temperature	80.00 °C
Comments	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[CMN.04.T22.047PGCE](#)