

## SUMMARY

### # Wires



*Image is for illustrative purpose only*

#### Series

Termination type No contacts / Accessory

IP rating 0

AWG wire size 0.00 - 0.00

Cable Ø 0.00 - 0.00 mm

Status active

#### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model DCC\*: Extraction/Installation tool for Fibre Optic type F1 and F2 contacts

Keying No keying

Housing Material

Weight 21.00 g

### Performance

Configuration

Insulator

Rated Current

### Specifications

Contact Type: Solder

### Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# DRAWINGS

No keying

---

## RECOMMENDED BY LEMO

Tools

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[DCC.91.312.5LA](#)