

SUMMARY

Wires



Image is for illustrative purpose only

Series

Termination type No contacts / Accessory

IP rating 0

AWG wire size 0.00 - 0.00

Cable Ø 0.00 - 0.00 mm

Status active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model DCG*: Spanners for hexagonal nuts

Keying No keying

Housing Material

Weight 83.71 g

Performance

Configuration

Insulator

Rated Current

Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS

No keying

Dimensions

	B	L	N
mm.	20	52	65
in.	0,79	2,05	2,56

RECOMMENDED BY LEMO

Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[DCG.91.201.4TN](#)