

SUMMARY

Wires

Low	0
High	0
Coax	0
Triax	0
Quad	0
Fiber	0
Fluidic	0

Image is for illustrative purpose only

Download

[Request a quote](#)

[Catalog](#)

Series

Termination type No contacts / Accessory

IP rating 0

Cable Ø 0.00 - 0.00 mm

Status active

Alternative part

TECHNICAL DETAILS

Mechanics

Shell Style/Model *:

Keying No keying

Housing Material Aluminium

Variant

Weight 4.91 g

Performance

Configuration

Insulator

Rated Current

Others

IP Rating: 0

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS

Draws

No keying

Dimensions

RECOMMENDED BY LEMO

Tools

None

Cables

121 221			
131 221			

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO](#):

[DCK.91.071.0LRC](#)