

## SUMMARY

### # Wires

Low	0
High	0
Coax	0
Triax	0
Quad	0
Fiber	0
Fluidic	0

*Image is for illustrative purpose only*

**Download**

[Request a quote](#)

### Series

Termination type	No contacts / Accessory
IP rating	0
Cable Ø	0.00 - 0.00 mm
Status	active
Alternative part	

## TECHNICAL DETAILS

### Mechanics

Shell Style/Model	DPE*: Crimping tool plier
Keying	No keying
Housing Material	
Variant	
Weight	351.81 g

### Performance

Configuration
Insulator
Rated Current

### Others

IP Rating: 0

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

---

# DRAWINGS

Draws

No keying

Dimensions

---

# RECOMMENDED BY LEMO

Tools

None

Cables

121 221			
131 221			

*LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[DPE.99.002.1K](#)