

SUMMARY

Wires

Low voltage	12
High voltage	1



Image is for illustrative purpose only

Series	3B
Termination type	Special contacts/None
IP rating	50
AWG wire size	30.00 - 22.00
Cable Ø	6.30 - 7.70 mm
Status	active
Matching parts	EGG.3B.712.CJL

Download

[Request a quote](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	FG*: Straight plug, cable collet and nut for fitting a bend relief
Keying	1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Housing Material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Variant	Z : Nut for fitting a bend relief

Performance

Configuration	3B.712 : 1 High V. 12 Low V.
Insulator	J: PEEK/PEEK
Rated Current	3 Amps

Specifications


Test voltage HV Ue (kV dc)	12
Test voltage HV Ue (kV rms)	8.5
Rated current HV (A)	4
Test voltage LV cont-cont sold.(kV rms)	1.2
Test voltage LV cont-shell sold.(kV rms)	0.85
Rated current LV (A)	5

Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): 5000
Temp (min / max): -55° C / +250° C
Humidity (max): <=95% [at 60 deg C /140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Climatical Category: 50/175/21
Shielding (min): 75 dB (10 MHz)
Shielding (min): 40 dB (1 GHz)
Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

	A	L	M	S1	S2
mm.	18	56.5	41.5	15	15
in.	0,71	2,22	1,63	0,59	0,59

RECOMMENDED BY LEMO

Tools

- Spanner wrench: [DCD.3B.040.PA150](#)
- Caps: [BFG.3B.100.PCSG](#)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[FGG.3B.712.CJYD72Z](#)