

SUMMARY

Wires

Low voltage	12
Fiber optic	1



Image is for illustrative purpose only

Series	3P
Termination type	Male solder
IP rating	61
AWG wire size	30.00 - 22.00
Cable Ø	6.70 - 7.50 mm
Status	active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	FG*: Straight plug with key and cable seal
Keying	User configurable, 1 of 11 key positions. Plug: male contacts; Receptacle: female contacts
Housing Material	PSU (Polysulfone), gray
Weight	19.48 g

Performance


Configuration	3P.92K : 1 FO (≤ 140 μ m) + 11 Low Voltage + 1 Ground contact
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	3 Amps

Others

Endurance (Shell):	>1000 mating cycles
Temp (min / max):	-50°C / +150°C
F ret (min):	100 N
F ret (max):	200 N
Steam sterilization:	20 times (with potting on rear connection)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS



Dimensions

	A	L
mm.	21.2	63
in.	0,83	2,48

RECOMMENDED BY LEMO

Tools

- Crimp settings: AWG/Selector = 20-22-24/6-5-5
- Replacement contact: EGG.3P.661.ZZY

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[FGG.3P.92K.PLWD75G](#)