

SUMMARY

Wires

Low voltage 8




Image is for illustrative purpose only

Series	5E
Termination type	Male solder
IP rating	68
AWG wire size	20.00 - 12.00
Cable Ø	19.60 - 20.50 mm
Status	active
Matching parts	PCA.5E.308.SLLC20

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	FZP*: Straight plug for remote handling, cable collet and inner anti-rotating device
Keying	Hermaphroditic keying (half moon insert) with male pin 1
Housing Material	Stainless steel shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces

Performance

Configuration	5E.308 : 8 Low Voltage
Insulator	L: PEEK (UL 94 / V-0/1.5)
Rated Current	22 Amps

Specifications

Contact Type: Solder
Vtest: 2100 V (AC), 2970 V (DC)


Others

Endurance (Shell): 5000 mating cycles
Temp (min / max): -55°C / +200°C
Humidity (max): <=95% [at 60 deg C / 140 F]
Vibration: 15 g [10 Hz - 2000 Hz]

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Shock Resistance: 100 g [6 ms]
Climatical Category: 50/175/21
Shielding (min): 95 dB (10 MHz)
Shielding (min): 80 dB (1 GHz)

DRAWINGS



Dimensions

	A	L	M	N	S1	S2
mm.	44	92	67	39.5	36	32
in.	1,73	3,62	2,64	1,56	1,42	1,26

RECOMMENDED BY LEMO

Tools

Caps: [BFA.5E.100.NAS](#)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

FZP.5E.308.SLAC20