

## SUMMARY

### # Wires

*Image is for illustrative purpose only*

|                  |                         |
|------------------|-------------------------|
| Series           | 3F                      |
| Termination type | No contacts / Accessory |
| IP rating        | 0                       |
| AWG wire size    | 0.00 - 0.00             |
| Cable Ø          | 5.30 - 16.00 mm         |
| Status           | active                  |

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |           |
|-------------------|-----------|
| Shell Style/Model | *:        |
| Keying            | No keying |
| Housing Material  |           |
| Weight            | 1.16 g    |

### Performance

|               |
|---------------|
| Configuration |
| Insulator     |
| Rated Current |

### Others

Temperature range in water steam: +140°C

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# DRAWINGS

No keying

---

## RECOMMENDED BY LEMO

Tools

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[GEC.3F.240.RA](#)