

SUMMARY

Wires

Low voltage	2
High voltage	2
Fiber optic	2
Series	3K
Termination type	Hybrid contacts
IP rating	68 when mated
AWG wire size	24.00 - 20.00
Cable Ø	8.90 - 9.50 mm
Status	active



Image is for illustrative purpose only

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	PE*: Fixed receptacle, nut fixing, cable adapter, with bend relief nut (back panel mounting)
Keying	5 keys (alpha=95, beta=115, gamma=20, delta=30, plug: female LV, male HV, female FO contacts)
Housing Material	
Variant	Z : Nut for fitting a bend relief
Weight	104.45 g

Performance

Configuration	3K.93C : 2 FO Type F2, 2 HV + 2 LV
Insulator	
Rated Current	10 Amps

Specifications

Cable type: SMPTE 311M or EBU R100


Others

Endurance (Shell): 20000 mating cycles
Temp (min / max): -40°C / +80°C

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Humidity (max): <=95% [at 60 deg C /140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Climatical Category: 50/175/21
Shielding (min): 95 dB (10 MHz)
Shielding (min): 80 dB (1 GHz)

DRAWINGS



Dimensions

	A	E	L	M
mm.	30	7.5	135	4.5
in.	1,18	0,30	5,31	0,18

RECOMMENDED BY LEMO

Tools

- Crimp settings: AWG/Selector = 20-22-24 14-16-18/6-5-5 7-6-5
- Positionner: [DCE.91.093.BVC](#)
- Positionner 2: [DCE.91.133.BVCM](#)
- Extractor: [DCC.09.05B.LAG](#)
- Extractor 2: [DCC.13.15B.LAG](#)
- Spanner: [DCP.91.023.TN](#)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Fiber Tool: [WST.KI.125.34](#)
Fiber Tool 2: [DCB.91.119.0TN](#)
Replacement contact: FG.3B.560.ZZC / EGW.3K.666.ZZM
Spanner wrench: [Socket for torque wrench DCM.65.270.AZ](#)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

LEMO:

[PEW.3K.93C.YSEC96Z](#)