

SUMMARY

Wires

Low voltage 6



Image is for illustrative purpose only

Series 2C
Termination type Female solder
IP rating 50
AWG wire size 28.00 - 20.00
Cable Ø 3.70 - 4.10 mm
Status **obsolete**

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model PCA*: Free receptacle, cable collet
Keying Hermaphroditic keying (half moon insert) with female pin 1
Housing Material Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Weight 17.05 g

Performance

Configuration 2C.306 : 6 Low Voltage
Insulator N: PBT (discontinued)
Rated Current 12 Amps

Specifications


Contact Type: Solder
Contact Dia.: 1.3 mm (0.051in)
Bucket Dia.: 1 mm (0.039in)
Max. Solid Conductor: 0.5 mm² (AWG 20)
Max. Stranded Conductor: 0.5 mm² (AWG 20)
R (max): 3.6 mOhm
Vtest: 1500 V (AC), 2100 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

Endurance (Shell): 500 mating cycles
Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

	A	L
mm.	14	28
in.	0,55	1,10

RECOMMENDED BY LEMO

Tools

Cables

CMN.06.T26.037QGZE	TPR (medical)	Grey	
60260	PTFE	White	

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[PCA.2C.306.CNLL42](#)