

SUMMARY

Wires



Image is for illustrative purpose only

Series	SP
Termination type	
IP rating	50
AWG wire size	0.00 - 0.00
Cable Ø	0.00 - 0.00 mm
Status	active

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model	DCE*: Positionner for female crimp contacts
Keying	
Housing Material	
Weight	13.22 g

Performance

Configuration	
Insulator	
Rated Current	4 Amps

Specifications

Test voltage d.c kV	12
Contact resistance	<8 mOhms

Others

Radiation resistance	10e6 Gray
Working temperature:	-20 deg C to + 125 deg C
Contact ret F (min):	40 N

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS



RECOMMENDED BY LEMO

Tools

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[SOE.050.VM](#)