



LEOPARD IMAGING INC



Rev. 1.2

LI-USB30-IMX226C

Data Sheet

Key Features

- USB 3.0 Super Speed support
- RAW data output without compression
- UVC compliance
- Color camera
- Support either CS or M12 lens
- Provide customization services
- USB +5VDC powered device
- Compact Size: 26mmx26mm
- 2 Boards are stacked
- Part#: **LI-USB30-IMX226C**



RAW data streaming



Camera Tool view mode



Default Lens Specification

- Model: N118B05518W
- Image format: 1/1.8"
- Focal length: 5.5 mm
- Aperture, F/#: 1.8
- Built in 650 nm IR cut filter
- FOV (D/H/V): 76 °/ 64.5 °/51 °

Applications

- Machine Vision
- Medical Camera
- Scientific Camera

SDK Supported

- Camera Tool Source Code in C#
- Capture & Display
- OpenCV supported through Emgu
- RAW to RGB Conversion
- Save file as BMP & RAW format
- Color matrix



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com
www.leopard-security.com

Specification

General Behavior	
Video Resolution @ Frame rate	4000 x 3000 @ 10 fps
Dynamic range	TBD
Interface (Optical)	
IR cut filter	Yes
Sensor specification	Sony Diagonal 9.33 mm (Type 1/1.7) CMOS Image Sensor IMX226
Shutter	Rolling
Color/Mono	Color
Format	1/1.7"
Total number of pixels	H:4168, V:3062
Pixel size	H:1.85 um, V: 1.85 um
Lens mount	CS / M12 lens mount support (Default: M12 lens)
Interface (Electrical)	
Interface	USB 3.0
Supply voltage	USB 3.0 +5 VDC power source
Current consumption	Approx. 156 mA at 5 VDC
Interface (Mechanical)	
Dimensions	L: 26 mm, W: 26 mm, H: 40 mm
Mass	28 g
Adjustment (Manual)	
Shutter	Support
Gain	Support
Adjustment (Auto)	
Shutter	Support
Gain	TBD
Environmental	
Max. temperature (operation)	0 °C ~ 50 °C (32 °F~ 122 °F)
Max. temperature (storage)	-20 °C ~ 80 °C (-4 °F~176 °F)
Max. humidity (operation)	20 % ~ 80 %, relative, non-condensing
Max. humidity (storage)	20 % ~ 80 %, relative, non-condensing



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com
www.leopard-security.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Leopard Imaging:](#)

[LI-USB30-IMX226C](#)