



LEOPARD IMAGING INC

LI-USB30-M021XB


Data Sheet

Applications

- Machine Vision
- Medical Camera
- Scientific Camera

SDK Supported

- Camera Tool Source Code in C#
- Capture & Display
- OpenCV supported through Emgu
- RAW to RGB Conversion
- Save file as BMP & RAW format



RAW data streaming



Key Features

- USB 3.0 Super Speed support
- RAW data output without compression
- UVC compliance
- USB 2.0 backwards compatible
- Support External Trigger, Software Trigger
- Support CS lens (Not include Lens)
- Provide customization services
- USB +5VDC powered device
- Part#:

LI-USB30-M021CB (Color)

LI-USB30-M021MB (Mono)



Camera Tool view mode



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com
www.leopard-security.com

Specification

General Behavior	
Video Resolution @ Frame rate	1280 x 960 @ 30 fps 1280 x 720 @ 60 fps 800 x 460 @ 90 fps 640 x 480 @ 30 fps
Sensitivity	TBD
Dynamic range	12 bit
Trigger mode	External Trigger, Software Trigger
Interface (Optical)	
IR cut filter	Yes
Sensor specification	Aptina MT9M021 Global Shutter 720p HD Sensor
Shutter	Global
Format	1/3"
Resolution	H:1280, V:960
Pixel size	H:3.75 um, V: 3.75 um
Lens mount	CS lens mount support
Interface (Electrical)	
Interface	USB 3.0
Supply voltage	USB 3.0 +5 VDC power source
Current consumption	Approx. 170 mA at 5 VDC
Interface (Mechanical)	
Dimensions	L: 30 mm, W: 30 mm, H: 30 mm
Mass (without lens)	30 g
Adjustment (Manual)	
Shutter	Support
Gain	Support (0 ~ 18 dB)
Adjustment (Auto)	
Shutter	Support
Gain	Support (0 ~ 18 dB)
Environmental	
Max. temperature (operation)	0 °C ~ 50 °C (32 °F~ 122 °F)
Max. temperature (storage)	-20 °C ~ 80 °C (-4 °F~176 °F)
Max. humidity (operation)	20 % ~ 80 %, relative, non-condensing
Max. humidity (storage)	20 % ~ 80 %, relative, non-condensing



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com
www.leopard-security.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Leopard Imaging:](#)

[LI-USB30-M021CB](#) [LI-USB30-M021MB](#) [LI-USB30-M021B](#)