



LEOPARD IMAGING INC

LI-USB30-P031XB


Data Sheet

Applications

- Machine Vision
- Medical Camera
- Scientific Camera

SDK Supported

- Camera Tool Source Code in C#
- Capture & Display
- OpenCV supported through Emgu
- RAW to RGB Conversion
- Save file as BMP & RAW format



RAW data streaming



Key Features

- USB 3.0 Super Speed support
- RAW data output without compression
- UVC compliance
- USB 2.0 backwards compatible
- Support External Trigger, Software Trigger
- Support CS lens (Not include Lens)
- Provide customization services
- USB +5VDC powered device
- Part#:
LI-USB30-P031CB (Color)
LI-USB30-P031MB (Mono)



Camera Tool view mode



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com
www.leopard-security.com

Specification

General Behavior	
Video Resolution @ Frame rate	2592 x 1944 @ 10 fps 1920 x 1080 @ 30 fps 640 x 480 @ 30 fps
Sensitivity	1.4 V/lux-sec
Dynamic range	12 bit
Trigger mode	External Trigger, Software Trigger
Interface (Optical)	
IR cut filter	Yes
Sensor specification	Aptina MT9P031 5M pixels Sensor
Shutter	Rolling
Format	1/2.5"
Resolution	H:2592, V:1944
Pixel size	H:2.2 um, V: 2.2 um
Lens mount	CS lens mount support
Interface (Electrical)	
Interface	USB 3.0
Supply voltage	USB 3.0 +5 VDC power source
Current consumption	Approx. 245 mA at 5 VDC
Interface (Mechanical)	
Dimensions	L: 30 mm, W: 30 mm, H: 30 mm
Mass (without lens)	30 g
Adjustment (Manual)	
Shutter	Support
Gain	Support
Adjustment (Auto)	
Shutter	Support
Gain	TBD
Environmental	
Max. temperature (operation)	0 °C ~ 50 °C (32 °F~ 122 °F)
Max. temperature (storage)	-20 °C ~ 80 °C (-4 °F~176 °F)
Max. humidity (operation)	20 % ~ 80 %, relative, non-condensing
Max. humidity (storage)	20 % ~ 80 %, relative, non-condensing



Leopard Imaging Inc.

1130 Cadillac Ct., Milpitas, CA 95035, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com
www.leopard-security.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Leopard Imaging:](#)

[LI-USB30-P031CB](#) [LI-USB30-P031MB](#)