



LEOPARD IMAGING INC

LI-IMX424-GMSL2-xxxH

Data Sheet

Key Features


- Sony Diagonal 9.69mm (Type 1/1.7) CMOS Image Sensor IMX424
- Optical format: 1/1.7"
- Number of active pixels: 3849H x 1929V
- Pixel size: 2.25 μm x 2.25 μm
- Output 12 bit Raw data
- Support 12V Power
- Lens: FOV H 40 / 65 / 120
- GMSL2 Serializer
- Connector: FAKRA Z TYPE
- Water proof: IP67
- Operation Temp: -40 ~ 85 $^{\circ}\text{C}$
- Storage Temp: -40 ~ 125 $^{\circ}\text{C}$
- Size: 30 x 30 x 29.2 mm
- Weight: 45 g
- Part#: **LI-IMX424-GMSL2-xxxH**



Application

- Automotive ADAS
- Automotive Rear View or Backup

Dimensions




Leopard Imaging Inc.

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

BOM







#	Name	SPEC	QTY/SET
1	Lens	DSL612 DSL608 Car-53	1
2	Screw	M2*8 cross flat head black ZINC	4
3	Shell 2	AL6061-T6 BLACK Anodizing	1
4	Sealing ring	Silicon rubber, White	1
5	LI-IMX424-MIPI-FKR	IMX424 sensor board	1
6	Copper pillar	M2*5+3	2
7	LI-GMSL2-FKR	GMSL2 board	1
8	O ring	6.5*1.5 Silicon rubber Red	1
9	Screw	M2*4 cross pan head black ZINC	2
10	Shell 1	AL6061-T6 BLACK Anodizing	1



Leopard Imaging Inc.

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA
 Phone: +1-408-263-0988
 Fax: +1-408-217-1960
 Email: sales@leopardimaging.com
 Website: www.leopardimaging.com

Camera boards Dimensions




Leopard Imaging Inc.

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA
 Phone: +1-408-263-0988
 Fax: +1-408-217-1960
 Email: sales@leopardimaging.com
 Website: www.leopardimaging.com

Water Proof

- Metal Housing
- Water-proof M12 lens
- Sealed Gasket (White)
- Sealed O-ring (Red)



Cable Connector

- Housing Connector- FAKRA Z Type
- Cable length: 3 meters
Support single Coax Cable transmit up to 12 meters
- Cable Part#: FAK-SMZSMZ-0008
- FAKRA type connectors




Leopard Imaging Inc.

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

Ordering Information

Note:

xxxH - 040H: FOV H 40°
065H: FOV H 65°
120H: FOV H 120°


LI-IMX424-GMSL2-040H	LI-IMX424-GMSL2-065H	LI-IMX424-GMSL2-120H
		
Lens: DSL612 Lens EFL: 11.9 mm F/#: 2.0 FOV(D): 44.5° FOV(H): 39° FOV(V): 20° Mount: M12	Lens: DSL608 Lens EFL: 7.9 mm F/#: 2.0 FOV(D): 71.5° FOV(H): 64.5° FOV(V): 32° Mount: M12	Lens: CAR-53 Lens EFL: 4.47 mm F/#: 1.6 FOV(D): 133.6° FOV(H): 118.7° FOV(V): 52.2° Mount: M16



Leopard Imaging Inc.

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

LI-GMSL2-DESER



Front View

LI-USB30-CNTL



Back View

LI-IMX424-GMSL2-xxxH can connect to USB 3.0 EVA module as a USB 3.0 camera.
Part#: **LI-USB30-IMX424-GMSL2-xxxH**

Key Features

- USB 3.0 Super Speed support
- RAW data output without compression
- UVC compliance
- Provide customization services
- 12VDC Power Supply
- Weight: 86 g
- Single Coax Cable transmit up to 12 meter PoC(Power over Cable)
- Support 3840x1928
- Power consumption: Approx. 91mA at 12VDC
- Support Windows, Linux OS and other OS which include UVC drivers

SDK Supported

- Camera Tool Source Code in C#
- Capture & Display
- Save file as BMP & RAW format
- Support register access function



Leopard Imaging Inc.

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

Revision History

Revision	Description	Release Date
1.0	First Release	17. Aug. 2018
1.1	Update lens information	24. Aug. 2018
1.2	Update the 120H lens to CAR-28	29. Apr. 2019
1.3	Add DSL608 and DSL612 lens	6. Aug. 2019



Leopard Imaging Inc.

48820 Kato Rd, Suite 100B, Fremont, CA 94538, USA
Phone: +1-408-263-0988
Fax: +1-408-217-1960
Email: sales@leopardimaging.com
Website: www.leopardimaging.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Leopard Imaging:

[LI-USB30-IMX424-GMSL2-065H](#) [LI-USB30-IMX424-GMSL2-070H](#) [LI-IMX424-GMSL2-040H](#) [LI-IMX424-GMSL2-065H](#)
[LI-IMX424-GMSL2-120H](#)