

Fingerprint Flash Drive AH650



Apacer AH650

Cutting-edge, Biometric Technology

Presented with a Stylish, Anti-theft Design

As USB flash drives become more popular with casual and business users alike, the need for increased data security to protect personal information and confidential files is crucial. To meet the need of users, Apacer now introduces the ultimate solution featuring biometric technology in portable data security: AH650.

Applications

- Desktop/laptop computers

Apacer AH650 is a USB flash drive with biometric fingerprint identification technology. Designed for those demanding the highest level of data protection, AH650 comprises public and hidden, fingerprint-secured partitions in which sensitive data can be saved to be safeguarded against unauthorized access attempts with fingerprint authentication. Your unique and unproducible fingerprint is the only key to unlock your data. Therefore, data stored in the hidden partition are safely protected. Compared with conventional flash drives, it not only provides ultimate security for computer users, but also spares the trouble of memorizing and entering long passwords. With AH650, the information age is free from password hassle; all you need is your finger.

Available in 32 GB and 64 GB capacities, AH650 is compatible with USB1.1, 2.0 and 3.0 specifications, providing a full range of alternatives for applications. Fusing state-of-the-art technology in biometric authentication and 360° finger presentation plane with a simple and sophisticated design, the drive is eye-catching at the first sight. On top of that, AH650 is easy to use. Simply plug in the device to a USB port on a computer, then all is at your fingertips.



Fingerprint Flash Drive AH650




Features:

- Capacity: 32 GB / 64 GB
- Compatible with Super Speed USB 3.0, 2.0 and 1.1 specifications
- Advanced fingerprint biometric technology
- Dual built-in partitions: public & fingerprint-secured partitions
- Supports up to 10 sets of fingerprints
- 360° finger presentation plane
- USB bus-powered
- Stylish and glossy finish colored with metallic pigments
- Strap hole design, easy to carry
- Pen cap design

Notes:

- Enrolling administrator's fingerprints upon first using AH650 is only supported on Windows XP and later. The device cannot be used under other environments, such as Mac and Linux, until the enrollment for administrators is completed.
- Administrators' accounts cannot be deleted once their fingerprints are enrolled. You can only change the identity of an administrator by replacing his fingerprints with someone else's. For detailed information, please refer to AH650 User's Manual.

Dimensions:



Fingerprint Flash Drive

AH650



General Product Specifications

Capacity*	32 GB, 64 GB
Interface	<ul style="list-style-type: none"> Standard USB head USB 3.0 Super Speed compliant Backward compatible with USB 2.0 & 1.1 specifications
System Requirements	<ul style="list-style-type: none"> Windows 10, Windows 8.1, Windows 8, Windows 7, Windows XP MAC OS 10.4.x or later Linux 2.6.x or later
Functionality	<ul style="list-style-type: none"> Plug and play Biometric authentication
Fingerprint Management Application	<ul style="list-style-type: none"> Enrolling fingerprints upon first use is only supported on Windows. Supports English/ Traditional Chinese /Simplified Chinese Stores a maximum of 10 sets of fingerprints
Voltage Requirement	DC5V± 10%
Operating temperature	0°C to 60°C (32°F to 140°F)
Storage temperature	-20°C to 60°C (-4°F to 140°F)
Dimensions (LxWxH)	64.4 x 22.8 x 10.3 mm
Weight	11g
Package contents	AH650 main unit
Certifications	CE, FCC, BSMI, RCM
Warranty	Limited product lifetime warranty (Please refer to Apacer website for warranty policy.)

*Unformatted. Theoretically, 1GB=1,000,000,000 Bytes. Under operating systems, the capacity might appear to be less than the theoretical capacity because the calculation in OS is based on 1 GB = 1024 MB / 1MB =1024KB and a minority of the capacity is reserved for maintenance purposes. The actual available memory on the device is less than what is listed on the package. This is due to small discrepancies in file formats and algorithms used by various operating systems. In addition, a portion of memory space is reserved for system files and data sectors for better performance.

** No USB cable comes with the package because the unit can only be used while directly plugged into a USB port on a computer. To avoid damages caused while using, please do not connect the unit to any device with a USB cable.

***For details, please refer to Apacer official website for warranty policy.

Global Offices

Taiwan (HQ)

Apacer Technology Inc.

Apacer Technology Inc.
1F., No.32, Zhongcheng Rd.,
Tucheng Dist., New Taipei City 236,
Taiwan R.O.C.
Tel: 886-2-2267-8000
Fax: 886-2-2267-2261
amtsales@apacer.com

U.S.A

Apacer Memory America, Inc.

46732 Lakeview Blvd., Fremont,
CA 94538
Tel: 1-408-518-8699
Fax: 1-510-249-9568
sa@apacerus.com

Japan

Apacer Technology Corp.

5F, Matsura Bldg., Shiba,
Minato-Ku Tokyo,
105-0014, Japan
Tel: 81-3-5419-2668
Fax: 81-3-5419-0018
jpservices@apacer.com

Europe

Apacer Technology B.V.

Science Park Eindhoven 5051 5692
EB Son,
The Netherlands
Tel: 31-40-267-0000
Fax: 31-40-267-0000#6199
sale@apacer.nl

China

Apacer Electronic (Shanghai) Co., Ltd

Room D, 22/FL, No.2, Lane 600,
Jieyun Plaza, Tianshan RD,
Shanghai, 200051, China
Tel: 86-21-6228-9939
Fax: 86-21-6228-9936
sales@apacer.com.cn

India

Apacer Technologies Pvt Ltd,

Unit No.201, Brigade Corner,
7th Block Jayanagar, Yediyur Circle,
Bangalore – 560082, India
Tel: 91-80-4152-9061
Fax: 91-80-4170-0215
sales_india@apacer.com

Fingerprint Flash Drive
AH650



Revision History

Version	Description	Date
1.0	Official release	12/16/2015

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Apacer:

[AP128GAH650C](#) [AP128GAH650S](#)