

# Apacer

The Most **Reliable**  
Storage For Industries



Industrial SD card



## Industrial SD card ISD H1-M

### Overview

Apacer Industrial Secure Digital 3.0 card is ideal for its high performance, good reliability and wide compatibility. Not to mention that it's well adapted for hand-held applications in semi-industrial/medical markets already. Apacer industrial SD card H1-M series providing wide range capacities from 4GB to 128GB fully compliant to SD3.0, and SD2.0 specifications are built with MLC NAND Flash and the latest firmware including read disturb , wear Leveling & Bad Block Management algorithms .Furthermore, by adapting very particular flash IC and IC packaging configuration, this product also has an optional industrial -45C to 85C extended temperature range version.



### Feature

- Compliant with SD 3.0 Specification
- S.M.A.R.T supported
- Wear-Leveling and Block Management
- Support Class 10 with UHS-I
- Low Power Consumption
- Wide Temperature Support(Optional)

## Specifications

Model	Industrial SD
Interface	SD3.0
NAND Flash Type	MLC
Capacity	SDHC:4GB~128GB
Sustained Read Performance (MB/sec)	Up to 43
Sustained Write Performance (MB/sec)	Up to 25
ECC Engine*	Built-in 42-bit per 1K bytes BCH ECC
Standard Operating Temperature ( °C )	-25 ~ + 85
Extended Operating Temperature ( °C )	-40 ~ + 85
Storage Temperature ( °C )	-40 ~ + 85
Shock	1,500G, 0.5ms
Vibration	20Hz~80Hz/1.52mm (frequency/displacement) 80Hz~2,000Hz/20G (frequency/accelerate)
Humidity	95%
Operating Voltage	3.3 V $\pm$ 5%
Low Power Consumption	Active mode: 145 mA & Idle mode: 235 uA
Dimension (L x W x H )	24x32x2.1 (mm)
MTBF (hours)	>3,000,000
Features / Technology	S.M.A.R.T./Wide Temp.
Applications	Military/Cloud Computing/In-Vehicle/Gaming/HealthCare/Embedded System

## Ordering Info

Model	Standard temp: -25~85	Extended temp: -40~85
4G	AP-ISD004GCA-1GTM	AP-ISD004GIA-1GTM
8G	AP-ISD008GCA-1GTM	AP-ISD008GIA-1GTM
16G	AP-ISD016GCA-1GTM	AP-ISD016GIA-1GTM
32G	AP-ISD032GCA-1GTM	AP-ISD032GIA-1GTM
64G	AP-ISD064GCA-1FTM	AP-ISD064GIA-1FTM
128G	AP-ISD128GCA-1FTM	AP-ISD128GIA-1FTM

## Global Presence

Taiwan (Headquarters)  
Apacer Technology Inc.  
Tel: +886-2-2267-8000  
Fax: +886-2-2267-2261

Japan  
Apacer Technology Corp.  
Tel: +81-3-5419-2668  
Fax: +81-3-5419-0018

Europe  
Apacer Technology B.V.  
Tel: +31-40-267-0000  
Fax: +31-40-290-0686

India  
Apacer Technologies Pvt. Ltd.  
Tel: +91-80-41529061~3  
Fax: +91-80-41700215

U.S.A.  
Apacer Memory America, Inc.  
Tel: +1-408-518-8699  
Fax: 1-510-249-9551

China  
Apacer Electronic(Shanghai)  
Co., Ltd.  
Tel: +86-21-6228-9939

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Apacer:

[AP-ISD064GCA-1FTM](#) [AP-ISD128GIA-1FTM](#) [AP-ISD064GIA-1FTM](#) [AP-ISD128GCA-1FTM](#) [AP-ISD032GCA-1GTM](#)  
[AP-ISD004GCA-1GTM](#) [AP-ISD032GIA-1GTM](#) [AP-ISD016GIA-1GTM](#) [AP-ISD016GCA-1GTM](#) [AP-ISD004GIA-1GTM](#)  
[AP-ISD008GIA-1GTM](#) [AP-ISD008GCA-1GTM](#)