



ENVIRONMENTAL SPECIFICATION

Item	Specification
Temperature	Operation: 0°C ~ 70°C Storage: -40°C ~ 85°C Junction temperature: max. 90°C for 5 minutes
Bending	10N
Torque	+/- 2.5 degree
Drop test	1.5m free fall

PHYSICAL MECHANICAL OUTLINE:

Dimensions Card Package	11mmx15mm Min. 10.9mmx14.9mm Max.11.1mmx15.1mm
Thickness	1.0mm +/- 0.1mm
Surface	Plain (except contact area)
Edges	Smooth edges
Inverse insertion	Protection on right corner (top view)

ORDERING INFORMATION

Speed	Capacity	P/N
Class4	4GB	AP4GMCSH4-X
	8GB	AP8GMCSH4-X
	16GB	AP16GMCSH4-X
	32GB	AP32GMCSH4-X

Global Offices

Taiwan (HQ)

Apacer Technology Inc.
1F., No.32, Zhongcheng Rd., Tucheng Dist., New Taipei City 236, Taiwan R.O.C.
Tel: 886-2-2267-8000
Fax: 886-2-2267-2261
amtsales@apacer.com

U.S.A

Apacer Memory America, Inc.
386 Fairview Way, Suite102, Milpitas, CA 95035
Tel: 1-408-518-8699
Fax: 1-408-935-9611
sa@apacerus.com

Japan

Apacer Technology Corp.
5F, Matsura Bldg., Shiba, Minato-Ku Tokyo, 105-0014, Japan
Tel: 81-3-5419-2668
Fax: 81-3-5419-0018
jpserives@apacer.com

Europe

Apacer Technology B.V.
Science Park Eindhoven 5051 5692 EB Son, The Netherlands
Tel: 31-40-267-0000
Fax: 31-40-267-0000#6199
sale@apacer.nl

China

Apacer Electronic (Shanghai) Co., Ltd
1301, No.251,Xiaomujiao Road, Shanghai, 200032, China
Tel: 86-21-5529-0222
Fax: 86-21-5206-6939
sales@apacer.com.cn

India

Apacer Technologies Pvt Ltd,
535, 1st Floor, 8th cross, JP Nagar 3rd Phase, Bangalore – 560078, India
Tel: 91-80-4152-9061
Sales_india@apacer.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apacer:](#)

[AP16GMCSH4-B](#) [AP8GMCSH4-B](#) [AP32GMCSH4-B](#)