

Fuse Block > 254 Series


254 Series OMNI-BLOK® Molded Base Fuse Block for 2AG Fuses





Dimensions [mm]

Solder & Q.C. Types:



Product Characteristics

Compatible Fuses Size	2AG			
Description	This low profile Omni-Blok® Fuse Block design is available with a choice of solder type terminals, Q.C. terminals or RC. board mountable terminals. The PCB design is offered with either tin-plated brass terminals for normal applications or tin-plated beryllium copper terminals for use in caustic environments. These fuse blocks feature individual barriers which reinforce the fuse clips while providing greater protection against clip damage and electrical shock. The unique design permits self-alignment of clips to fuse cap. This, plus a one-piece clip/terminal assures low contact resistance. Multiple units may be broken apart to obtain desired number of units.			
Rating	400 VAC/DC, 10A			
Dielectric Strength	1500V Minimum			
Clip/Terminals	Tin-Plated Spring Brass, except pn 254121 is Tin-Plated Beryllium Copper			
Base	Black Thermoplastic, glass reinforced with UL V0 flammability rating			
Ambient Temperature	-40°C to +85°C			


Agency Approval

Agency	Agency File Number				
c FL °us	E14721				
(7316				

OPTIONS:

- 1. Other colors available on special order. Contact factory.
- 2. Two different style clips can be supplied for circuit identity or polarization. Contact factory.

P.C. Board Mount Type



Additional Information







Resources



Samples

Cartridge Fuse Blocks

Fuse Block > 254 Series

Ordering NO.*	Catalog NO.	No. of Poles	Width (B)	Width [mm]	Clip/Terminal Material	Packaging Available
			Solder Type Terminals	5		
02540001Z	254 001	1	0.35"	[8.6]	Brass	Z
02540002Z	254 002	2	0.875"	[22.2]	Brass	Z
02540003Z	254 003	3	1.31"	[33.3]	Brass	Z
02540004Z	254 004	4	1.75"	[44.5]	Brass	Z
02540005Z	254 005	5	2.18"	[55.4]	Brass	Z
02540006Z	254 006	6	2.62"	[66.5]	Brass	Z
02540007Z	254 007	7	3.06"	[77.7]	Brass	Z
02540008Z	254 008	8	3.50"	[88.9]	Brass	Z
		NEM	A Style .110" Q.C.Terr	ninals		
02540201Z	254 201	1	0.35"	[8.6]	Brass	Z
02540202Z	254 202	2	0.875"	[22.2]	Brass	Z
02540203Z	254 203	3	1.31"	[33.3]	Brass	Z
02540204Z	254 204	4	1.75"	[44.5]	Brass	Z
02540205Z	254 205	5	2.18"	[55.4]	Brass	Z
02540206Z	254 206	6	2.62"	[66.5]	Brass	Z
02540207Z	254 207	7	3.06"	[77.7]	Brass	Z
02540208Z	254 208	8	3.50"	[88.9]	Brass	Z
			P.C. Board Mount			
02540101Z	254 101	1	0.35"	[8.6]	Brass	Z
02540121Z	254 121	1	0.35"	[8.6]	Beryllium Copper	Z

Add Suffix:

Z = for bulk package

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

02540204Z
02540202Z
02540004Z
02540207Z
02540001Z
02540201Z
02540003Z
02540006Z
02540208Z

02540206Z
02540002Z
02540122Z
02540205Z
02540007Z
02540203Z
02540005Z
02540101Z
02540121Z

02540008Z
02540008Z
02540008Z
02540000Z
02540000Z