



356/359 Screw Terminal Laminated Base Terminal for 3AG/AB Fuses



Dimensions



Fuse Type	A	B	C	D	E
3AG/3AB	See ordering information	2.38" [60.5 mm]	.25" [6.4 mm]	.91" [23.1 mm]	.73" [18.5 mm]

Additional Information

356 Series



Resources
356 Series



Samples
356 Series

359 Series



Resources
359 Series



Samples
359 Series

Product Characteristics

Compatible Fuse Size	3AG/AB
Electrical	356 Series: 600 Vac/dc 15 A 359 Series: 600 Vac/dc 30 A
Clip/Terminals	356 000 Series: Nickel-plated spring brass 359 000 Series: Silver-plated beryllium copper
Terminals	B-32THD screw type
Base	Black phenolic laminate.
Mounting Hole	3AG Block: Reference Dimensions .142" / .147" [3.6/3.7 mm] diameter with .295" / .302" [7.5/7.7 mm] x .82" [20.8 mm] C.S.
Operation Temperature	-40 °C to +125 °C

Agency Approvals

Agency	Agency File Number
UL US	E14721

Ordering Information

# of Poles	Dimension "A" [mm]	Ordering Number	
1	.78" [19.8]	03560001Z	03590001Z
2	1.69" [42.9]	03560002Z	03590002Z
3	2.59" [65.8]	03560003Z	03590003Z
4	3.50" [88.9]	03560004Z	03590004Z
5	4.41" [112.0]	03560005Z	03590005Z
6	5.31" [134.9]	03560006Z	03590006Z
7	6.21" [157.7]	03560007Z	03590007Z
8	7.12" [180.8]	03560008Z	03590008Z
9	8.03" [204.0]	03560009Z	03590009Z
10	8.94" [227.1]	03560010Z	03590010Z
11	9.84" [250.0]	03560011Z	03590011Z
12	10.75" [273.1]	03560012Z	03590012Z

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[03590012Z](#) [03560006Z](#) [03590008Z](#) [03560009Z](#) [03560010Z](#) [03560003Z](#) [03560002Z](#) [03590005Z](#) [03590001Z](#)
[03560012Z](#) [03590003Z](#) [03590004Z](#) [03590010Z](#) [03560001Z](#) [03590009Z](#) [03560008Z](#) [03590002Z](#) [03590006Z](#)
[03590007Z](#) [03560004Z](#) [03560007Z](#) [03560005Z](#) [03560011Z](#) [03590011Z](#)