342 Series


Panel Mount Enclosed Fuseholders for 3AG/AB Fuses






Dimensions


General Application / Straight Terminal Product Dimensions



General Application / Right Angle Terminal Product Dimensions



Watertight Product Dimensions







Product Characteristics

	General Application Products	Watertight Product			
Compatible Fuses	3AG/AB				
Electrical	Rated at 20 amperes for any voltage up to 250				
Ambient Temperature	-40°C to +85°C				
Dielectric Strength	2400 volts minimum	1500 volts minimum			
Mounting	Withstands 15 lb in. mounting torque; maximum panel thickness: .187"	Withstands 15 lb in. mounting torque; maximum panel thickness is .250"			
Molded Parts	Black thermoplastic (UL94 V-0)	Black thermoset (UL94 V-0)			
Seal	Neoprene washer provide drip-proof protection on the front side of the panel (upon request)	O-ring provides a watertight seal on the front side of the panel per MIL-PRF-19207			
Terminals	Copper & copper alloy. Tin plated, except '4" Quick-Connect terminals are nickel plated	Copper & copper alloy. Tin plated			
Hardware	Comes with a mounting nut and neoprene washer	O-rings (2) and hex nut, unassembled			
Ingression Protection Rating	IP40	IP67			

Agency Approvals

Agency	Agency File Number	
<i>7</i> .	E14721	
(7316 (*Except 342 006)	

Ordering Information

	•				
Body Terminal Type		Catalog Number			
Angle	Connect	Fluted Knob	Knurled Knob		
General Application Products					
Straight	Solder	342 014	342 012		
	3/16" Q.C.	342 038	342 058		
	1/4" Q.C.	342 838	342 858		
Right Angle	Solder	342 004	342 022		
	3/16" Q.C.	342 028	342 048		
	1/4" Q.C.	342 828	342 848		
Watertight Product					
Straight	Solder	342 006 *	Not Applicable		

Note: Refer to Fuseology for information on proper fuseholder re-rating.

Additional Information







Resources

Accessories

Samples

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

03420104HX040 03420012HX010 03420001X 03420838HX010 03420828X 03420004HXP 03420028HXL 03420004HXPL 03420848X 03420828H 03420038X 03420028X 03420838HXP 03420858HXL 03420014H 03420838H 03420058HXL 03420058X 03420048HXL 03420858H 03420858HXP 03420012HXL 03420848H 03420012X 03420858HXPL 03420012HXP 03420848HXL 03420038H 03420014HXL 03420048X 03420028H 03420014X 03420838HXL 03420058H 03420006ZXA 03420012HXP 03420022X 03420038HXL 03420022HXL 03420048HXL 03420048HXL 03420048HXL 03420022HXL 03420048HXL 03420006ZXA 03420048HXPL 03420022H 03420004H 03420004HXL 03420004HXL 03420004HXL 03420004HXL 03420004HXL 03420006ZXA 03420038HXA 03420004X