

FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 58V

RoHS


Specifications

Housing:	Out of thermoplastic (UL 94-V0, heat-resistant)
Connections:	Leaf spring connector systems, soldering terminals (4 pins each), copper alloy, tinned
Color:	Black

Ordering Information

Part Number	Package Size
178.4265.0002	500


Dimensions

Dimensions in mm


Description

PCB Fuse Holder for 42V PowerNet with coding for TAC fuses-links. For through hole soldering. Rated voltage 58V.

Recommended Assembly



Note: The locking feature at the holder center must lock holder and PCB before welding.



Ratings

Part Number	Description	Contact Temperature
178.4265.0002	Complete	max. 130°C



Visit Littelfuse.com for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.

FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 80V

RoHS


Specifications


Housing:	Out of thermoplastic (UL 94-V0, heat-resistant)
Connections:	Leaf spring connector systems, soldering terminals (4 pins each), copper alloy, silver plated
Color:	Black

Ordering Information

Part Number	Package Size
178.6165.xxx1	100
178.6165.xxx2	500

Dimensions

Dimensions in mm



Description

PCB Fuse Holder for ATO / FKS size fuse-links. For through hole soldering. Rated voltage 80V.

Recommended Assembly

Note: The locking feature at the holder center must lock holder and PCB before welding.

Ratings

Part Number	Description	Contact Temperature
178.6165.000_	Complete	max. 130°C



Visit Littelfuse.com for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.

FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 80V


RoHS


Specifications

Housing:	Out of thermoplastic (UL 94-V0, heat-resistant)
Connections:	Leaf spring connector systems, soldering terminals, copper alloy, tin plated
Color:	Black


Ordering Information

Part Number	Package Size
178.6164.xxx1	100
178.6164.xxx2	500

Description


PCB Fuse Holder for ATO/FKS size fuse-links. For through hole soldering. Rated voltage 80V

Recommended Assembly



Note: The locking feature at the holder center must lock holder and PCB before welding.

Dimensions in mm



Ratings

Part Number	Description	Contact Temperature
178.6164.000_	Complete	max. 130°C



Visit Littelfuse.com for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[178.4265.0002](#) [178.6165.0001](#) [178.6165.0002](#) [178.6164.0001](#) [178.6164.0002](#)