


# **AUTO LINK PAL FUSES - 294C**





#### **Specifications**

Voltage Rating: 32 VDC Current Cycling: 24°C

The fuses satisfy the performance requirements after 50% of the rated current is applied for 10,000 cycles. Each cycle consists of an interrupted current with the pattern of 5 minutes ON and 10 minutes OFF.

Operating Temperature Range: -40°C to +125°C

Complies with JASO 0612

## **Ordering Information**

Part Number	Package Size	
0294xxx.MXJ-C	1000	

## **Description**

PAL fuses are commonly found on many Japanese and domestic built vehicles.

#### **Time-Current Characteristics**


% of Rating	Opening Time Min / Max (s)	
110	14,400 s	
200	5 s / 100 s	
350	0.2s / 7 s	
600	0.040 s / 1 s	

## **Ratings**

Part Number	Current Rating (A)	Body Color
0294020	20	LIGHT BLUE
0294030	30	PINK
0294040	40	GREEN
0294050	50	RED
0294060	60	YELLOW
0294070	70	BROWN
0294080	80	BLACK
0294100	100	BLUE
0294120	120	WHITE

#### **Dimensions**

Dimensions in mm



## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Littelfuse:

0294120.T 0294030.U 0294040.MXJ 0294050.HXJ-C 0294080.H 0294070.U 0294070.T 0294070.HXJ-C 0294030.MXJ-C 0294070.HXJ-C 0294030.MXJ-C 0294070.HXJ-C 0294030.MXJ 0294060.MXJ-C 0294060.MXJ-C 0294060.MXJ-C 0294050.H 0294120.U 0294060.H 0294070.MXJ 0294120.MXJ 0294070.T 0294040.MXJ-C 0294050.T 0294040.U 0294050.U 0294030.HXJ-C 0294100.MXJ-C 0294080.HXJ-C 0294080.HXJ-C 0294050.MXJ 0294050.U 0294070.H 0294120.H 0294070.H 0294070.H 0294070.H 0294040.HXJ-C 0294060.HXJ-C 0294060.HXJ-C