

LIQUID LEVEL PROBES & PROBE HOLDERS

LIQUID LEVEL CONTROL ELECTRODES		
Product	Features	Accessory For
<div>LLP-24</div> <div>Liquid Level Probe</div> <div></div>	Threaded stainless steel probe measuring 24 in. (61 cm) long. Designed for use with PHST-38QTN liquid level control electrodes.	<div>PHST-38QTN</div>
<div>PHST-38QTN</div> <div>Probe Holder</div> <div>P0700-409</div> <div>Protective Boot</div> <div></div>	Designed for use with all conductive liquid level controls. Composed of insulators and metal parts made of number 300 series stainless steel. These internally conductive probe holders are designed for a maximum steam pressure of 240 PSI; 400° F maximum. Maximum voltage from electrode to ground. PHST-38QTN is UL 353 Recognized.	<div>Series:</div> <div>LLC1 LLC2 LLC4</div> <div>LLC5 LLC6 LLC8</div> <div>PC-XXX-LLC-CZ</div> <div>PC-XXX-LLC-GM</div> <div>460-15-100-LLS</div>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[PHST-38QTN](#) [LLP-24](#)