



ATO[®] Shunt

ATO[®] Shunt

Specifications

*Recommended Environmental Temp.:	-40°C to +125°C
Max. Continuous Load Rating:	35A * *
Housing Material:	Thermoplastic (UL 94 Flammability Rating V0)
Terminal Material:	Tin Plated Brass



*Tin plating's temperature limit is ≈130°C
**Rating varies based on mating terminal performance

Ratings

Part Number	Max Continuous Load Rating** (A)	Housing Material	Terminal Material	Part Quantity
02400094P	35	Thermoplastic (UL 94V0)	Tin Plated Brass	2000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[0495900.Z](#) [02400094P](#) [0297900.WXNV](#) [0327900.YX2S](#)