

ISO MINI RELAYS

Single Pole, Dual Throw



Description

Littelfuse ISO Mini Relays are compact, modular, general purpose relays that allow you to tailor your vehicle's hard wired box for the capability that you need. Adhering to the ISO 280 form factor, these relays plug into existing, standard ISO 280 boxes along with fuses or other components. Littelfuse has a broad offering of Form C (Single Pole, Dual Throw) plug-in mini relays in 20A and 40A, 12V/24V, bracketed, and sealed versions.

Web Resources

Download 2D print and technical resources at:
littelfuse.com/55025

Ordering Information

PART NUMBER	DESCRIPTION	AMPERAGE	VOLTAGE RATING	MOUNTING	SEALED/UNSEALED
RC-200124-DN *	20A, 24V Mini Relay with Diode & Snap-In Bracket	20A	24V	Panel	Unsealed
RC-200124-NN *	20A, 24V Mini Relay with Snap-In Bracket	20A	24V	Panel	Unsealed
RC-400112-DS *	40A, 12V Mini Relay with Diode & Sealing	40A	12V	Plug in	Sealed
RC-400112-DN *	40A, 12V Mini Relay with Diode & Snap-In Bracket	40A	12V	Panel	Unsealed
RC-400112-NN *	40A, 12V Mini Relay with Snap-In Bracket	40A	12V	Panel	Unsealed
RC-400112-RN *	40A, 12V Mini Relay with Resistor & Snap-In Bracket	40A	12V	Panel	Unsealed

* Box and Retail Blister Pack Available

Features and Benefits

- Compact, modular design allows for tailored HWB solutions
- Off-the-shelf plug-in relay capability
- Industry standard ISO 280 form factor
- Bracketed versions available for panel mounting
- Sealed version available to prevent contamination

Applications

- Lighting Control
- Starting Control
- Horn Control
- Heating & Cooling Control
- Fan Control

Specifications Overview

Circuitry:	SPDT
Housing:	Plastic
Contacts:	Silver Alloy

Recommended Products



Relay Socket
PN:99026

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[RC-400112-DN](#) [RC-400112-RN](#) [RA-400112-DN](#) [RC-400012-DS](#) [RC-400112-NN](#) [RA-400112-NN](#) [RC-200124-DN](#)
[R2-400112-RN](#) [RC-200124-NN](#)