



75908 SERIES SINGLE POLE BATTERY DISCONNECT SWITCHES



75908



75908 Back

Description

The 75908 battery disconnect switch is a 300A, 36V Single Pole, Single Throw (SPST) manual disconnect switch that can be used to disconnect the battery from the vehicle electrical system. Disconnecting the battery from the electrical system prevents potential thermal events and ensures system shut down during maintenance or emergency. Battery disconnect switches also prevent parasitic loads from draining the battery during inactivity.

Web Resources

Download 2D print and technical resources at:
littelfuse.com/75908

Ordering Information

PART NUMBER	DESCRIPTION
75908 *	300A, 36V, SPST Battery Disconnect Switch

* Box and Blister Pack Available

Features and Benefits

- Rugged steel case
- Sealed between shaft and mounting stem; case and terminal insulator
- Fits panels up to 1/4" (6.4mm) thick
- Anti-rotation locator pin enables ease of mounting

Specifications Overview

Amperage:	300A
Max Input Current:	2000A
Voltage Rating:	36V DC
Circuitry:	Single Pole, Single Throw
Housing:	Plated Steel
Contacts:	2 Copper Studs (1/2-20)

Applications

- Heavy Duty Truck
- Construction
- Emergency Vehicles
- Bus/Transit
- Agriculture



Visit Littelfuse.com for the most up-to-date product information. Littelfuse products are designed for specific applications and should not be used for any purpose (including, without limitation, automotive applications) not expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse product documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[75908](#)