




额定负荷 Ratings	DC 16V 0.1A
初期接触电阻 Initial Contact Resistance	100m Ω Max
绝缘电阻 Initial Insulation Resistance	DC 250V 60 \pm 5Sec.10M Ω Min.
抗电强度 Dielectric	AC 100V(50~60HZ) 60 Sec.
扭力 Operating Force	150 \pm 100gf.cm
负荷寿命 Operating Life With Load	10,000次
接触行程 Pre Travel	45°(旋转)
回路 Poles-Throws	1P8T

[illegible]

Technical drawing of a mechanical part, showing a top view and a side view. The top view is a rectangular plate with rounded corners, featuring two circular holes with diameters of 13.8 and 16. The side view shows a cross-section with a thickness of 5.4 and a central hole with a diameter of 13. Dimensions are given in millimeters.

7	接触片	CONTACT	C5210R	1	Ag CLAD				
6	弹片	SPRING PLATE	SUS	2	NATURAL				
5	端子	TERMINAL	C2680R	1	Ag PLATED				
4	胶壳	HOUSING	PA	1	BLACK C				
3	盖片	COVER	SUS	1	NATURAL	A02	增加备栏内的表面处理及颜色	刘红梅	06-04-28
2	旋钮	ROTARY KNOB	PA	1	BLACK C	A01		方 勇	2005/10/4
1	胶柄	KNOB	PA	1	BLACK C	标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
序 NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS	DWG NO. ITEM2565				

TOLERANCES UNLESS OTHERWISE SPEC.		TITLE	ROTARY SWITCH		ITEM NO	RW-108-NS RT		
UNDER 1	± 0.10	DRAWN	刘红梅	06-04-28	VERSION	A02	PAGE 1 OF 1	
1 - 10	± 0.30	REVIEWED	张念明	06-04-29	SCALE		UNIT	mm
OVER 10	± 0.50	APPROVED	高 洪	06-04-29	PROJECTION		 	

COMAX ELECTRONICS (HUIZHOU) CO.,LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Switches:](#)

[RW108NSRT](#)