

FP Series Sealed Ultra Miniature Pushbutton Switches




A
Pushbutton

Features/Benefits

- Ultra-miniature pushbutton
- Multiple poles and throws
- Long life 100,000 cycles
- Vertical and right angle mount
- Sealed against soldering and cleaning processes
- Optional caps
- RoHS compliant

Typical Applications

- Networking equipment
- High-end consumer
- Professional instrumentation
- Computer, Server, Modem & Data storage



Specifications

CONTACT RATING: Max. 0.4 VA (28 V DC or V AC)
 ELECTRICAL LIFE: 50,000 cycles (FP11 & FP21)
 10,000 cycles (FP12 & FP22)
 CONTACT RESISTANCE: (10mA @ 2 V DC) 80 mΩ max. initial
 INSULATION RESISTANCE: 500MΩ min. @ 500 V DC - 1 minute
 OPERATING TEMPERATURE: -20°C to 80°C
 SOLDERABILITY: Per MIL-STD-202F method 208D, or
 EIA RS-186E method 9
 PACKAGING:
 Tray pack - 25 pcs per tray (A1 type terminal)
 - 100 pcs per tray (C1 type terminal)
 Caps (optional) - Bulk bag; 100 caps per bag.

Materials

MOVABLE CONTACTS:
 Base metal: Phosphor bronze
 Plating: Gold over nickel plate
 FIXED CONTACTS:
 Base metal: Brass
 Plating: Gold over nickel plate
 COVER: PA66 - Black
 ACTUATOR: PPS - Black
 BASE: PPS - Black
 SUPPORT BRACKET: Steel with tin plate
 (A1 type terminal only)

NOTE: Specifications and materials listed above are for switches with standard options.
 For information on specific and custom switches, consult Customer Service Center.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages A-106 thru A-107. For additional options not shown in catalog, consult Customer Service Center.





Designation FP11 SPST N.O. FP12 SPDT N.O. FP21 DPST N.O. FP22 DPDT N.O.	Actuator Length SP Standard plunger 3.3mm	Terminal Style C1 Vertical A1 Right Angle	Contact Plating B1 Gold over nickel plate	Packaging TP Tray packaging	Cap 00 No cap 01 White cap - bulk bagged 02 Black cap - bulk bagged 03 Red cap - bulk bagged
--	--	--	--	--	---



FP Series Sealed Ultra Miniature Pushbutton Switches




Pushbutton
A

SWITCH CIRCUIT






CIRCUIT	MODEL NO.	SWITCH FUNCTION		SCHEMATIC
		POS. 1	POS. 2	
				
SPST	FP11	OFF	MOM	
		CONNECTED TERMINALS		
		OPEN	1-3	
SPDT	FP12	ON	MOM	
		CONNECTED TERMINALS		
		2-3	2-1	
DPST	FP21	OFF	MOM	
		CONNECTED TERMINALS		
		OPEN	1-3,4-6	
DPDT	FP22	ON	MOM	
		CONNECTED TERMINALS		
		2-3,5-6	2-1,5-4	

TERMINAL STYLE

C1 VERTICAL



A1 RIGHT ANGLE



FP Series Sealed Ultra Miniature Pushbutton Switches




A

Pushbutton


ACTUATOR LENGTH

SP STANDARD PLUNGER 3.3MM



CAPS

OPTION CODE	DESCRIPTION
00	NO CAP
01	WHITE CAP, BULK BAGGED
02	BLACK CAP, BULK BAGGED
03	RED CAP, BULK BAGGED



To purchase Caps separately without switch, please use these part numbers


PART #	COLOR
798D01000	WHITE
798D02000	BLACK
798D03000	RED

MOUNTING HOLE


C1 VERTICAL




FP11




FP12







FP21



FP22



A1 RIGHT ANGLE



Dimensions are shown: mm
Specifications and dimensions subject to change

C&K

13 Mar 20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Switches:](#)

[FP11SPC1B1TP00](#) [FP11SPC1B1TP01](#) [FP11SPC1B1TP02](#) [FP11SPC1B1TP03](#) [FP11SPA1B1TP00](#)
[FP11SPA1B1TP01](#) [FP11SPA1B1TP02](#) [FP11SPA1B1TP03](#)